


# Self Tapping Screws

## Self Tapping Screws - Pan Head



RoHS10

TANB  
TANBS



Type	Material	Surface Treatment
TANB	SWCH Equivalent	Trivalent Chromate
TANBS	SUS304 Equivalent	-

M	A	E	Phillips No.
3	5.5	2.0	2
3.5	6.0	2.3	2
4	7.0	2.6	2
5	9.0	3.3	2

Part Number	M-L	TANB				TANBS			
		Unit Price	Volume Discount Rate			Unit Price	Volume Discount Rate		
Type		1-29 pc(s)	30-99	100-249	250-500	1-29 pc(s)	30-99	100-149	150-500
TANB TANBS	3 - 5					-	-	-	-
		6							
		8							
		10							
	3.5 - 6	12							
		8							
		10							
		12							
	4 - 6	16							
		8							
		10							
		12							
5 - 8	16								
	10								
	12								
	20								




Ordering Example Part Number  
**TANBS4-10**

## Self Tapping Screws - Flat Head



RoHS10

TASA  
TASAS



Type	Material	Surface Treatment
TASA	SWCH Equivalent	Trivalent Chromate
TASAS	SUS304 Equivalent	-

M	A	E	Phillips No.
3	6.0	1.75	2
3.5	7.0	2.00	2
4	8.0	2.30	2
5	10.0	2.80	2

Part Number	M-L	TASA				TASAS			
		Unit Price	Volume Discount Rate			Unit Price	Volume Discount Rate		
Type		1-29 pc(s)	30-99	100-249	250-500	1-29 pc(s)	30-99	100-149	150-500
TASA TASAS	3 - 6								
		8							
		10							
		12							
	3.5 - 8	10							
		12							
		4 - 8							
		10							
	5 - 10	12							
		16							
		20							




Ordering Example Part Number  
**TASAS4-10**

## Self Tapping Screws - Truss Head



RoHS10

TATR  
TATRS



Type	Material	Surface Treatment
TATR	SWCH Equivalent	Trivalent Chromate
TATRS	SUS304 Equivalent	-

M	A	E	Phillips No.
3	6.9	1.9	1
3.5	8.1	2.2	2
4	9.4	2.5	2
5	11.8	3.1	2

Part Number	M-L	TATR				TATRS			
		Unit Price	Volume Discount Rate			Unit Price	Volume Discount Rate		
Type		1-29 pc(s)	30-99	100-249	250-500	1-29 pc(s)	30-99	100-149	150-500
TATR TATRS	3 - 6								
		8							
		10							
		12							
	3.5 - 6	8							
		10							
		12							
		4 - 6							
	5 - 8	8							
		10							
		12							
		16							
20									



Ordering Example Part Number  
**TATR5-10**