

# Steel Wheel Conveyors

For Option Parts, see p. 8-1294/For Single Wheels, see p. 8-1296 The number next to the logo mark indicates items in stock for each brand.

Conveyors

Steel Roller Conveyors

Stainless Steel Roller Conveyors

Aluminum Roller Conveyors

Resin Roller Conveyors

Extension Roller Conveyors

Wheels Conveyors

Ball Casters Units

Upward Ball Casters

Downward Ball Casters

Upward/Downward Combined Use Ball Casters

Cleanroom Type Ball Casters

Ball Casters for Special Purpose

Motor Pulleys, Motor Rollers

Belt Conveyors

Mini Belt Conveyors


Belts



## Wheel Conveyor (wheel diameter 50mm)



- Features**
- When the line setting is complete, it can convey about 1000kg. It is suitable for heavy load.
- Use**
- For conveying heavy objects.
- Specs**
- Wheel: Precut
  - Load per wheel: 60kg
  - Wheel width: 13mm
- Materials**
- Frame: Steel
  - Wheel: Steel
- Origin**
- Japan



MISUZU KOKI Co.Ltd.

Order Unit: 1 Piece | Factory direct | No freight charge | Excluding remote islands |

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Pitch (mm)	Conveyor Length (mm)	SPQ (piece)	Weight (kg)
★465-8973	MWH50T-0718	¥21,756	¥29,300	75	1800	1	11.8
★465-8981	MWH50T-0724	¥27,249	¥36,700	75	2400	1	15.0
★465-8990	MWH50T-1018	¥18,711	¥25,200	100	1800	1	11.3
★465-9007	MWH50T-1024	¥23,166	¥31,200	100	2400	1	13.0


Contact us:059-397-3220 <http://www.misuzukoki.jp/>



## Wheel Conveyor (wheel diameter 40mm)



- Features**
- It is a conveyor that uses rubber lining wheels.
- Use**
- For conveying items which you don't want to scratch.
- Specs**
- Load per wheel: 30kg
  - Wheel width: 9mm
  - Mounting Bolt: With carriage M8 x 20L 2 sets
- Materials**
- Frame: Steel
  - Wheel: Steel with black rubber lining
- Origin**
- Japan



TRUSCO NAKAYAMA CORPORATION


Order Unit: 1 Piece | Factory direct | No freight charge | Excluding remote islands |

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Pitch (mm)	Conveyor Length (mm)	SPQ (piece)	Weight (kg)
★300-5887	V-40G-50-1800	¥23,735	¥25,640	50	1800	1	6.3
★300-5895	V-40G-50-2000	¥26,457	¥28,580	50	2000	1	7.0
★300-5909	V-40G-50-2400	¥31,613	¥34,150	50	2400	1	8.4
★300-5917	V-40G-50-3000	¥39,482	¥42,650	50	3000	1	10.5
★300-5925	V-40G-75-1800	¥17,162	¥18,540	75	1800	1	5.3
★300-5933	V-40G-75-2000	¥18,690	¥20,190	75	2000	1	5.9
★300-5941	V-40G-75-2400	¥22,856	¥24,690	75	2400	1	7.1
★300-5950	V-40G-75-3000	¥28,540	¥30,830	75	3000	1	8.9
★300-5968	V-40G-100-1800	¥13,886	¥15,000	100	1800	1	4.8
★300-5976	V-40G-100-2000	¥15,413	¥16,650	100	2000	1	5.4
★300-5984	V-40G-100-2400	¥18,486	¥19,970	100	2400	1	6.5
★300-5992	V-40G-100-3000	¥23,059	¥24,910	100	3000	1	8.1


Contact us:0120-509-849 <http://www.orange-book.com/>



## Wheel Conveyor (wheel diameter 48mm)



- Features**
- The steel wheels are lined with black synthetic rubber.
- Use**
- For conveying items that gets scratched easily.
- Specs**
- Load Per Wheel: 10kg
  - Wheel Width: 12mm
- Materials**
- Frame: Steel
  - Wheel: Steel with black rubber lining
- Origin**
- Japan



TERAUCHI CORPORATION


Order Unit: 1 Piece | Factory direct | Shipping not included |

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Pitch (mm)	Conveyor Length (mm)	SPQ (piece)	Weight (kg)
★462-4629	KR-A6BG-P50X1500L	¥12,191	¥12,900	50	1500	1	4.5
★462-4637	KR-A6BG-P50X1800L	¥14,459	¥15,300	50	1800	1	5.5
★462-4645	KR-A6BG-P50X2000L	¥16,065	¥17,000	50	2000	1	6.0
★462-4653	KR-A6BG-P75X1500L	¥8,883	¥9,400	75	1500	1	3.9
★462-4661	KR-A6BG-P75X1800L	¥10,584	¥11,200	75	1800	1	4.8
★462-4670	KR-A6BG-P75X2000L	¥11,718	¥12,400	75	2000	1	5.1
★462-4564	KR-A6BG-P100X1500L	¥7,182	¥7,600	100	1500	1	3.5
★462-4572	KR-A6BG-P100X1800L	¥8,600	¥9,100	100	1800	1	4.3
★462-4581	KR-A6BG-P100X2000L	¥9,545	¥10,100	100	2000	1	4.7
★462-4599	KR-A6BG-P150X1500L	¥5,670	¥6,000	150	1500	1	3.2
★462-4602	KR-A6BG-P150X1800L	¥6,710	¥7,100	150	1800	1	4.0
★462-4611	KR-A6BG-P150X2000L	¥7,655	¥8,100	150	2000	1	4.2


Contact us:072-259-4584 <http://www.tsconveyor.co.jp/>



## Wheel Conveyor (wheel diameter 48mm)



- Features**
- The steel wheels are lined with urethane rubber.
- Use**
- For conveying items that gets scratched easily.
- Specs**
- Load Per Wheel: 10kg
  - Wheel Width: 12mm
- Materials**
- Frame: Steel
  - Wheel: Steel with urethane rubber lining
- Origin**
- Japan



TERAUCHI CORPORATION

Order Unit: 1 Piece | Factory direct | Shipping not included |

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Pitch (mm)	Conveyor Length (mm)	SPQ (piece)	Weight (kg)
★462-4742	KR-A6UG-P50X1500L	¥26,933	¥28,500	50	1500	1	4.5
★462-4751	KR-A6UG-P50X1800L	¥32,130	¥34,000	50	1800	1	5.5
★462-4769	KR-A6UG-P50X2000L	¥35,721	¥37,800	50	2000	1	6.0
★462-4777	KR-A6UG-P75X1500L	¥18,711	¥19,800	75	1500	1	3.9
★462-4785	KR-A6UG-P75X1800L	¥22,397	¥23,700	75	1800	1	4.8
★462-4793	KR-A6UG-P75X2000L	¥25,043	¥26,500	75	2000	1	5.1
★462-4688	KR-A6UG-P100X1500L	¥14,553	¥15,400	100	1500	1	3.5
★462-4696	KR-A6UG-P100X1800L	¥17,388	¥18,400	100	1800	1	4.3
★462-4700	KR-A6UG-P100X2000L	¥19,373	¥20,500	100	2000	1	4.7
★462-4718	KR-A6UG-P150X1500L	¥10,679	¥11,300	150	1500	1	3.2
★462-4726	KR-A6UG-P150X1800L	¥12,758	¥13,500	150	1800	1	4.0
★462-4734	KR-A6UG-P150X2000L	¥14,459	¥15,300	150	2000	1	4.2

Contact us:072-259-4584 <http://www.tsconveyor.co.jp/>