


Safety Protection Materials

Corner Covers


Adhesion to rubbers remains stable as a special adhesive which follows rubbers is used.

Corner Covers 10mm Width



PRGLSS (Rubber Type: Black)

For Corners
PRGLFCFS (Rubber Type: Black)



RoHS10

- Can be affixed on angled sections of 90°.
- Adhesive is applied on the inside surface.

Material Main Body: Ethylene Rubber (EPDM) Hardness: Shore A60
Adhesive Part: Acrylic Adhesives


Corner Covers 10mm Width

Part Number	L Selection	Weight (g)	Unit Price
PRGLSS	100	3	
	500	15	
	1000	30	
	1500	45	
	2000	60	

For Corners


Part Number	Unit Price
PRGLFCFS	

Corner Covers 20mm Width



PRGLS (Rubber Type: Black)
PRGLF (Soft Type)
PRGLFG (Soft Type, Light Gray)

For Corners
PRGLFC (Soft Type)
PRGLFCG (Soft Type, Light Gray)



- Can be affixed on angled sections of 90°.
- Adhesive is applied on the inside surface.

Part Number	Material		Hardness
	Main Body	Adhesive Part	
PRGLS	Ethylene Rubber (EPDM)	Acrylic Type	Shore A60
PRGLF, PRGLFG, PRGLFC, PRGLFCG	EPDM Foam	Adhesive	Shore A20


Corner Covers 20mm Width

Part Number	L Selection	Weight (g)	Unit Price
PRGLS	100	14	
	500	70	
	1000	140	
	1500	210	
	2000	280	
PRGLF PRGLFG	100	10	
	500	50	
	1000	100	
	1500	150	
	2000	200	

For Corners


Part Number	Unit Price
PRGLFC PRGLFCG	

Corner Covers 34mm Width



PRGLM (Rubber Type: Black)
PRGLMG (Rubber Type: Light Gray)

For Corners
PRGLMC (Rubber Type: Black)
PRGLMCG (Rubber Type: Light Gray)



- Can be affixed on angled sections of 90°.
- Adhesive is applied on the inside surface.

Material Main Body: Ethylene Rubber (EPDM) Hardness: Shore A60
Adhesive Part: Acrylic Adhesives

Corner Covers 34mm Width

Part Number	L Selection	Weight (g)	Unit Price
PRGLM PRGLMG	100	30	
	500	150	
	1000	300	
	1500	450	
	2000	600	

For Corners


Part Number	Unit Price
PRGLMC PRGLMCG	

Corner Covers 50mm Width



PRGLL

For Corners
PRGLLC (For Corners)



- Can be cut with a utility knife.
- Properties see the Ethylene Rubber of P391

Material: Ethylene Rubber (EPDM) Hardness: Shore A60

Corner Covers 50mm Width

Part Number	L Selection	Weight (g)	Unit Price
PRGLL	100	98	
	500	490	
	1000	980	
	1500	1470	
	2000	1960	

For Corners

Part Number	Unit Price
PRGLLC	

Ordering Example	Part Number	L
	PRGLSS	100
	PRGLS	100
	PRGLM	100

How to Mount




Drill holes and fix with screws, etc.



Example

Table Corner



For use as safety bumper on equipment and pillars.

