

Note that, for some of the types shown here, order might be unable to be received by the MISUMI Malaysia, Indonesia and/or India offices.

Hex Socket Set Screws / Hex Socket Cap Screws / Crush Pads


Soft Tips / Head Cap Screws

Hex Socket Set Screws Soft Tips



RoHS 10

Type	M Thread's Material	S Surface Treatment	M Pad Material
SBPP	SCM435	Black Oxide	Polyacetal (White)
SBCP			Free-cutting Brass (C3604BD)
SBCT			Urethane (Shore A70, Black)
SBPPS	SUS304 Equivalent	-	Polyacetal (White)
SBCPS			Free-cutting Brass (C3604BD)
SBCTS			Urethane (Shore A70, Black)



Part Number		L						S	d	B	C (Min.)		
Type	M (Coarse)	Ⓢ Dimensions in () are only applicable to SBPP and SBCP.											
SBPP	SBCP	3	5	6	8	10	12	16	20	0.5	1.5	1.5	2.0
SBPPS	SBCPS	4	6	8	10	12	16	20		1	2	2	2.5
SBPP	SBCP	5		8	10	12	16	20	25	1	3	2.5	3.0
SBPPS	SBCPS	6		8	10	12	16	20	25	30	40	3	3.5
		8		10	12	16	20	25	30	40	50	4	5.0
SBCT		10		12	16	20	25	30	40	50	(60)	5	6.0
SBCTS		12		16	20	25	30	40	50	(60)	(80)	6	8.0
				16	20	25	30	40	50	(60)	(80)	(100)	

M (Coarse)	Unit Price					
	SBPP	SBCP	SBCT	SBPPS	SBCPS	SBCTS
3			-			-
4			-			-
5						
6						
8						
10						
12						




Ordering Example
Part Number - L
SBPP10 - 50

Hex Socket Set Screws Head Cap Screws



RoHS 10

Type	M Thread	S Surface Treatment	M Pad Material
CBPP	SCM435	Black Oxide	Polyacetal (White)
CBPCP			Free-cutting Brass (C3604BD)
CBPPS	SUS304 Equivalent	-	Polyacetal (White)
CBCPS			Free-cutting Brass (C3604BD)




Part Number	M (Coarse)	L	A	E	S	d	B	(e)	CBPP		CBPCP		CBPPS		CBCPS	
									Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate
CBPP (Plastic Pad)	3	10 15 20	5.5	3	0.5	1.5	2.5	0.5	1 ~ 99 pc(s)	100 - 500 pcs	1 ~ 99 pc(s)	100 - 500 pcs	1 ~ 99 pc(s)	100 - 500 pcs	1 ~ 99 pc(s)	100 - 500 pcs
CBPPS	4	10 15 20	7	4	1	2	3	0.6								
	5	15 20 30	8.5	5	1	3	4	0.6								
CBPCP (Brass Pad)	6	15 20 30	10	6	1	4	5	0.7								
CBCPS	8	20 30 40	13	8	2	6	6	1.0								

Crush Pads



Ⓢ 50 pcs. per Pkg.


SEPN
SEPNs (Thin)
(50 pcs. per Pkg.)
PACK-SEPN
PACK-SEPNs



M Material: C3604BD



Example




Ⓢ Use it for shaft fixing.

Part Number	Applicable M	d	t		C	PACK-SEPN, PACK-SEPNs	
			SEPN	SEPNs		Unit Price 1 to 100 (Single item)	Unit Price / Volume Discount Rate
SEPN	*3	2.2	2.0	0.5	*0.2		1 ~ 3 pkg(s). / 4 ~ 100 pkg(s).
SEPNs	*4	3.0	2.5				
PACK-SEPN	*5	3.9	3.0				
(50 pcs. per Pkg.)	*6	4.7	3.5	1.0			
	8	6.4	4.5	-			
PACK-SEPNs	10	8.2	5.5	-	*0.3		
(50 pcs. per Pkg.)	12	9.9	6.5	-			



Example



Ⓢ Use this set piece to prevent set screw from damaging the mating material.

Ⓢ SEPNs is available only in M3 through M6. * For SEPNs, C<0.1 Ⓢ PACK-SEPNs is available only in M3 through M6.
Ⓢ When placing an order for PACK-SEPN or PACK-SEPNs, please specify number of packages. 1 package to be delivered includes 50 pieces.



Ordering Example
Part Number
CBPP3-10
SEPN5
PACK-SEPN4