



RAYCHEM | RAYCHEM CGPT

TE Internal #: 5069732014

Clear, 2:1, Single Wall Tubing, Shrinks To .187 in [4.8 mm],  
Irradiated Modified Polyolefin, .375 in [9.5 mm] Inner Diameter,  
RAYCHEM CGPT

[View on TE.com >](#)

Heat Shrink Tubing > CGPT 2:1 Heat Shrink Tubing



Primary Product Color: **Clear**

Wall Type: **Single Wall**

Expanded Inside Diameter (Min): **9.5 mm [ .375 in ]**

Recovered Inside Diameter (Max): **4.8 mm [ .187 in ]**

Shrink Ratio: **2:1**

[All CGPT 2:1 Heat Shrink Tubing \(257\)](#)

## Features

### Product Type Features

Wall Type	Single Wall
-----------	-------------

### Electrical Characteristics

Operating Voltage (Max)	.6 kV
-------------------------	-------

### Body Features

Fluid Type	Gasoline, Hydraulic Fluid, Lubricating Oil
Primary Product Color	Clear
Shrink Ratio	2:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Flexible

### Dimensions

Recovered Wall Thickness (Tolerance)	.15 mm[.006 in]
Recovered Wall Thickness (Nominal)	.65 mm[.026 in]
Product Length	1220 mm[48.031 in]
Expanded Inside Diameter (Min)	9.5 mm[.375 in]
Recovered Inside Diameter (Max)	4.8 mm[.187 in]
Tubing Size Range	4.8 – 9.5 mm[.187 – .375 in]