


Flange Type U-NUT (stainless)

Features

- No need washer, can be improved work efficiency.
- Can be reducing the number of parts.
- Can be achieved stable locking performance.
- Excellent corrosion resistance.
- The appearance can be improved by the FUJILOK U-NUT with integrated washer.
- Only coarse thread (pitch) is available.



Thread Accuracy: ISO6H (JIS6H) Unit: mm

Material of the Nut Body												SUS304		
Material of the Friction Ring												SUS301		
Nominal Diameter (d)	Pitch (p)	Width Across Flat (s)		Flange Diameter (ødc)		Overall Height (h)		Thread Height (m) Approx.	Across Corners (e) Approx.	Flange Thickness (c) MIN	Unit Weight (g) Approx.	Reference Tightening Torque (N·m) Bolt		
		Base	Tolerance	Base	Tolerance	Base	Tolerance					Proof Stress 300 N/mm ²	Strength grade 50 210 N/mm ²	Strength grade 70 450 N/mm ²
M 6	1	10	0 -0.2	14.2	0 -0.4	6.9	±0.3	6.0	11.5	1.1	3.7	7.0	4.9	10.0
M 8	1.25	13	0 -0.25	17.5	0 -0.4	9.0	±0.4	7.8	15.0	1.2	7.7	17.0	12.0	25.0
M10	1.5	17	0 -0.25	23.0	0 -0.5	11.0		9.6	19.6	1.5	16.7	33.0	23.0	50.0
M12	1.75	19	0 -0.35	26.5	0 -0.5	13.0		11.5	21.9	1.8	24.8	58.0	41.0	88.0

* Please check the stock condition of each size. * The material also includes items with equivalent materials. * Dimensions may change for improvement.

Introduction of Applications



Tunnel Illumination Lamps



Safety Nets



Snowmobiles