


メスユニオン (PT)

SA




継手の呼び	適用管外径A		(PT) T	E	六角対辺			I	ℓ	手締め L(約)
	呼び径	外径			H ₁	H	H			
SA - 6×1/8	6	6	1/8	4	17	14	7	25	35.5	
SA - 8×1/4	8	8	1/4	6	19	17	7	30	40.5	
SA - 10×1/4	10	10	1/4	8	19	19	7	30	41.5	
SA - 10×3/8	10	10	3/8	8	24	19	7	32	43.5	
SA - 12×1/4	12	12	1/4	10	19	22	7	30	41.5	
SA - 12×3/8	12	12	3/8	10	24	22	7	32	43.5	
SA - 15×3/8	15	15	3/8	12	24	27	7.5	34	46.5	
SA - 15×1/2	15	15	1/2	12	30	27	7.5	39	51.5	
SA - 16×1/2	16	16	1/2	13	30	30	7.5	39	51.5	
SA - 18×1/2	18	18	1/2	14	30	32	8	39	51.5	
SA - 20×3/4	20	20	3/4	17	36	36	8	41	53.5	
SA - 22×3/4	22	22	3/4	18	36	36	9	41	53.5	
SA - 25×3/4	25	25	3/4	20	36	41	10	41	54.5	
SA - 25×1	25	25	1	20	46	41	10	45	58.5	
SA - 28×1	28	28	1	22	46	46	10	47	61	
SA - 30×1	30	30	1	25	46	46	10	47	61.5	
SA - 30×1 1/4	30	30	1 1/4	25	55	46	10	51	65.5	
SA - 32×1 1/4	32	32	1 1/4	26	55	50	11	51	65.5	
SA - 35×1 1/4	35	35	1 1/4	28	55	55	11	51	68.5	
SA - 38×1 1/2	38	38	1 1/2	32	65	60	12	51	70.5	
SA - 40×1 1/2	40	40	1 1/2	32	65	60	12	55	74.5	
SA - 42×1 1/2	42	42	1 1/2	34	65	60	12	55	74.5	
SA - 50×2	50	50	2	40	80	75	12	60	81.5	
SA - 1/8×1/4	1/8	10.5	1/4	8	19	19	7	30	41.5	
SA - 1/4×3/8	1/4	13.8	3/8	11	24	24	7.5	34	46	
SA - 3/8×1/2	3/8	17.3	1/2	14	30	32	8	39	51.5	
SA - 1/2×3/4	1/2	21.7	3/4	18	36	36	9	41	53.5	
SA - 3/4×1	3/4	27.2	1	22	46	46	10	47	61	
SA - 1×1 1/4	1	34.0	1 1/4	28	55	55	11	51	68.5	
SA - 1 1/4×1 1/2	1 1/4	42.7	1 1/2	34	65	65	12	55	75.5	
SA - 1 1/2×2	1 1/2	48.6	2	40	80	75	12	60	81.5	

※Average Values

※上記諸元は品質の向上により若干変わることがあります。

隔壁ハーフユニオン (メス)

JC



継手の呼び	適用管 外径A	(PT) T	E	六角対辺			I	ℓ ₁	ℓ	手締め L(約)	N	最大 S
				H ₁	H ₂	H						
JC - 6×1/8	6	1/8	4	17	17	14	7	32	13	42.5	M12×1.5	13
JC - 8×1/4	8	1/4	6	19	19	17	7	32	18	42.5	M14×1.5	13
JC - 10×1/4	10	1/4	8	19	22	19	7	32	18	43.5	M16×1.5	13
JC - 10×3/8	10	3/8	8	24	22	19	7	32	20	43.5	M16×1.5	13
JC - 12×1/4	12	1/4	10	19	24	22	7	32	18	43.5	M18×1.5	13
JC - 12×3/8	12	3/8	10	24	24	22	7	32	20	43.5	M18×1.5	13
JC - 15×3/8	15	3/8	12	24	27	27	7.5	37	20	49.5	M22×1.5	15
JC - 15×1/2	15	1/2	12	30	27	27	7.5	37	25	49.5	M22×1.5	15
JC - 16×1/2	16	1/2	13	30	30	30	7.5	37	25	49.5	M24×1.5	15
JC - 18×1/2	18	1/2	14	30	32	32	8	39	25	51.5	M26×1.5	15
JC - 20×3/4	20	3/4	17	36	32	36	8	39	27	51.5	M28×1.5	15
JC - 22×3/4	22	3/4	18	36	36	36	9	39	27	51.5	M30×1.5	15
JC - 25×3/4	25	3/4	20	41	41	41	10	39	27	52.5	M35×1.5	15
JC - 25×1	25	1	20	46	41	41	10	39	31	52.5	M35×1.5	15
JC - 28×1	28	1	22	46	46	46	10	41	31	55	M38×1.5	15
JC - 30×1	30	1	25	46	46	46	10	41	31	55.5	M40×1.5	15
JC - 30×1 1/4	30	1 1/4	25	55	46	46	10	41	35	55.5	M40×1.5	15
JC - 32×1 1/4	32	1 1/4	26	55	46	50	11	43	35	57.5	M42×1.5	15

※Average Values

※上記諸元は品質の向上により若干変わることがあります。