

規格 Specifications

品番 Article number	呼称 Specification	内径(mm) Inside dia.		厚み (mm) Thickness	最大カット長(mm) Max cut length		材質 Material
		収縮前 Before shrinkage	収縮後 After shrinkage		標準 Standard	特注 ^(注1) Special order ^(Note1)	
GRC	17P	19	16.5	0.5	1200	3600	PFA
	20P	21	18.5	0.5	1200	3600	
	22P	24	19.5	0.5	1200	3600	
	25P	26	21.5	0.5	1200	3600	
	27P	30	24	0.5	1200	3600	
	30P	33	27	0.5	1200	3600	
	35P	36	29.5	0.5	1200	3600	
	40P	43	35	0.5	1200	3600	
	50P	51	40	0.5	1200/1800		
	55P	57	49	0.5	1200		
	60P	63	50	0.5	1200/1800	3600	
	65P	67	54	0.5	1800		
	70P	71	61	0.5	1800		
	75P	75	61	0.5	1800		
	80P	81	64	0.5	1800		
	85P	91	74	0.5	1800		
	95P	98	82	0.5	1800		
	100P	106	85	0.5	1800/3600		
105P	109	86	0.5	1800			
115P	117	96	0.5	1800			
125P	127	106	0.5	1800/3600			
130P	136	107	0.5	1800/3600			
140P	144	125	0.5	1800			
150P	154	125	0.5	1800/3600			

GRC	160F	163	131	0.5	3600		FEP
	170F	174	133	0.5	3600		
	180F	190	163	0.5	4000		
	200F	206	164	0.5	4000		
	215F	220	166	0.5	4000		
	230F	235	185	0.5	4000		
	240F	249	187	0.5	4000		
	250F	259	206	0.5	4000		
	265F	278	245	0.5	4000		
	280F	298	246	0.5	4000		
	290F	305	247	0.5	4000		
	300F	316	247	0.5	4000		

※お問い合わせ・ご注文時には、対象ロールの正確な直径・面長をご連絡ください。最適なチューブを選定いたします。

※カット長については400mm以上で100mmピッチでカット販売いたします。1本より御用命ください。

※保管は必ず冷暗所(30℃以下)にて行ってください。自然収縮の恐れがあります。

※PはPFA製、FはFEP製です。

※収縮後内径は200℃、10分間加熱時の測定値であり保証値ではありません。

注1:特注ロングサイズは成形時の金型跡が残ります。加熱収縮することで金型跡は消えますが表面精度を必要とする用途では必ずお客様にて試験・検証を行い使用可否をご判断ください。

* Please inform us of the exact dia and length of the Roll when equally or order. A suitable product will be selected accordingly.

* Cut length is 400 mm or above, with a pitch of 100 mm. Any quantity of tube order is welcome.

* Product specifications are subject to modification without notice.

* Please store the tubing in a cool and dark location (30°C or below). At higher temperatures, there is a possibility that the tube will shrink.

* P Indicates a PFA product, and F Indicates an FEP product.

* The inside diameter after shrinkage is the measurement made after heating to 200°C for 10 minutes. It is not a guaranteed value.

Note1: Specially ordered long-size product might have die mark as a result of forming. Please check at your side beforehand especially on the condition that surface accuracy is necessary.