


EAG-CF

ERGOSTYLE BRIDGE HANDLES




ELESA Original Design EBP.FLX




Handle	Cap	Insert
Polypropylene plastic	Polyamide plastic	Brass
Black matte	Black Matte, Orange Matte, Gray Matte, Yellow Matte, Light Blue Matte, Red Matte	

Part Number	A	B	C	D	E	F	G	H	J	K	Weight (g)
EAG140CF	144	39	92	26	8.5	8.5	26.5	13.5	8.5	117	56
EAG180CF	178	45	122	28	9.5		32		14	150	67



·Can be mounted on diameters of 300mm to 600mm.



- Working temperature : Between 0°C and 80°C
- Use in hot or highly humid circumstances can deteriorate the plastic material properties.
- A handle and caps are packed separately and not delivered in assembly.


Part Number	Mounting-Hole Centers Distance
EAG140CF	$f_1=0.044 \times D_1 + 81.5$
EAG180CF	$f_1=0.056 \times D_1 + 102.8$

Strength Data

Part Number	F1[N]	F2[N]
EAG140CF	1000	1000
EAG180CF	1000	1000

Ordering Example

EAG140CF - BR		Color Code	Cap Color
Part Number	Color Code	OG	Orange
		GR	Gray
		YE	Yellow
		LB	Light Blue
		BR	Black
		RE	Red



Tensile Stress

·The stated F1 and F2 values denote the average of the breaking loads measured in a breaking test under normal working conditions.

