

Body

Glass-fiber reinforced
polyamide plastic
Black matte


Part Number	A	B	C	D	Weight (g)	Sales Unit	Proper Ergostyle Bridge Handles		
EAG110SS	22.5	18	6.5	53	14	2 Pcs./Set	EAG110C	EAG110B	-
EAG140SS	26.5	19.5	8.5	58.5	18		EAG140C	EAG140B	EAG140CF
EAG180SS	29	20.5	8.5	65.5	22		EAG180C	EAG180B	EAG180CF

- Use with **EAG** and **EAG-CF** Ergostyle Bridge Handles.
- Working temperature : Between -30°C and 130°C
- Use in hot or highly humid circumstances can deteriorate the plastic material properties.

Strength Data


Part Number	F ₁ [N]	F ₂ [N]	L ₁ [J]	L ₂ [J]
EAG110SS	1600	1500	8	3
EAG140SS	2200	1800	10	4
EAG180SS	2200	1500	12	5

Tensile Stress



•The stated F1 and F2 values denote the average of the breaking loads measured in a breaking test under normal working conditions.

Impact Strength



•The stated L1 and L2 values denote the average of the breaking loads measured in a drop test with a load of 6.7N.