

# EFPH-SL

# ERGOSTYLE PULL HANDLES



ELESA Original Design EPR-PF



**EFPH-SL-CL**  
(Gray White)



**EFPH-SL**  
(Black)



Body
Glass-fiber reinforced polyamide plastic
Black matte
Gray White


Gray White	Black	A	B	C	D	E	F	G	H	J	Weight (g)
Part Number	Part Number										
<b>EFPH 90SL-CL</b>	<b>EFPH 90SL</b>	90	50	19	17	17.5	76	79	28	7	20
<b>EFPH120SL-CL</b>	<b>EFPH120SL</b>	120	95	28.5	24	26.5	94	103	58	11	58

- Easy snap-in installation.
- Use in hot or highly humid circumstances can deteriorate the plastic material properties.
- Working temperature : Between 0°C and 80°C

## Strength Data

Type		F <sub>1</sub> [N]	F <sub>2</sub> [N]
<b>EFPH-SL</b>	90	1800	500
<b>EFPH-SL-CL</b>	120	1000	250

## Load Capacity




The stated values denote the average of loads measured in breaking tests under normal working conditions.

## Installation Instructions




1. Set the handle's upper rear part into the cutout, and then push in its lower part.



2. The snap-in mechanism locks the handle.

## Mounting Cutout



Deburr the edge before installing a handle.

c (Panel Thickness)	90		120	
	a(+0.2)	b(±0.1)	a(+0.2)	b(±0.1)
Over 0.7 to 0.8	85	34.9	107.5	70.6
Over 0.8 to 1.2		35.1		70.9
Over 1.2 to 1.5		36.1		71.3
Over 1.5 to 2				71.6
Over 2 to 2.2				