


NK35-2B




Standard Sprocket Two-row B-type

Order No. Example


NK35-2B 15



Ground Specification Welded Specification



Ground Specification



Welded Specification

- Chain No.35-2
- Chain Pitch (P)9.525mm
- Bushing Link Inner Width ... (W)4.78 mm
- Bushing Outside Diameter ... (Dr)5.08 mm
- Tooth Width (T)4.1 mm (M)14.2mm

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d			Boss Diameter BD	Boss Length BL	Shape	Material	Weight kg	¥	Semi-F
				Prepared Product	Minimum	Maximum							¥
NK35-2B	10	35	30.82	10	11	12	20	30	Ground Specification	Carbon Structural Steel High-frequency Hardened Teeth	0.10		
	11	38	33.81	10	11	12	23	30			0.11		
	12	41	36.80	10	11	14	26	30			0.14		
	13	44	39.80	10	11	14	27	30			0.17		
	14	47	42.81	10	11	18	32	30			0.21		
	15	51	45.81	10	11	20	35	30			0.25		
	16	54	48.82	10	11	20	38	30			0.29		
	17	57	51.84	10	11	22	41	30			0.34		
	18	60	54.85	10	11	25	44	35			0.45		
	19	63	57.87	10	11	28	47	35			0.51		
	20	66	60.89	12	13	30	50	40			0.64		
	21	69	63.91	12	13	30	50	40			0.64		
	22	72	66.93	12	13	32	55	40			0.67		
	24	78	72.97	15	16	38	60	40			0.82		
	25	81	76.00	15	16	38	60	40			0.92		
	28	90	85.07	15	16	42	65	45			1.26		
30	96	91.12	15	16	42	65	45	1.34					
32	102	97.18	15	16	42	65	45	1.43					
40	127	121.40	15	16	42	65	45	2.30					
45	142	136.55	19	20	55	83	45	2.84	Welded Specification	Common Steel			
50	157	151.70	19	20	55	83	45	3.22					
60	187	182.00	19	20	63	93	50	4.70					



Sprocket No. and Quantity



* Since we also manufacture sizes other than those in the catalog, and machine shaft holes/keys/taps, etc., depending on your request, please contact our company's sales office for details.



Same-day shipping

* Please refer to P24 to P33 for the Semi-F Series <Complete Product> order method.