


LSM

LINEAR-MOTION STOPPERS



| Body | Handle / Spacer | Ring Nut | Push Bar |
|---|--|--|--------------|
| Steel (S45C) Electroless nickel plated | Steel (SCM440) Quenched and tempered Electroless nickel plated | Steel (SCM435) Quenched and tempered Electroless nickel plated | Steel (S45C) |



| Part Number | Linear-Rail Width (Nominal) | A | B | C | D | E | F | G | H | J | K | L | M |
|-------------|-----------------------------|-----|----|----|----|----|----|------|------|----|----|----|----|
| LSM-20 | 20 | 63 | 26 | 22 | 63 | 13 | 16 | 11.5 | 7.8 | 14 | 76 | 73 | 23 |
| LSM-25 | 25 | 70 | 30 | 24 | | 15 | 18 | 13.5 | 9.5 | | | | |
| LSM-30 | 30 | 90 | 36 | 30 | 80 | 18 | 22 | 15.5 | 10.6 | 18 | 95 | 92 | 27 |
| LSM-35 | 35 | 100 | 38 | 34 | | 24 | 24 | 18.5 | 13.4 | | | | |

| Part Number | N | Handle Operating Load (N) | Holding Force (N) | Weight (g) |
|-------------|-----------------|---------------------------|-------------------|------------|
| LSM-20 | M5×0.8 10-deep | 40 | 150 | 283 |
| LSM-25 | M6×1 12-deep | | | 376 |
| LSM-30 | M8×1.25 14-deep | 50 | 250 | 729 |
| LSM-35 | | | | 932 |