


# HG40A

## ● Order No. Example

### HG40A 20H

Type      No. of Teeth  
└──────────┘  
Sprocket No.



- Chain ..... No.40
- Chain Pitch ..... (P)12.70mm
- Roller Link Inner Width ..... (W) 7.95mm
- Roller Outside Diameter ..... (Dr) 7.92mm
- Tooth Width ..... (T) 7.2 mm

**m** Carbon Structural Steel

**h** High-frequency Hardened Teeth

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d		Weight kg	¥	Semi-F ¥
				Prepared Hole Product	Minimum			
HG 40A	11H	51	45.08	10	11	0.09		
	12H	55	49.07	10	11	0.10		
	13H	59	53.07	12	13	0.12		
	14H	63	57.07	12	13	0.14		
	15H	67	61.08	12	13	0.16		
	16H	71	65.10	13	14	0.18		
	17H	76	69.12	13	14	0.20		
	18H	80	73.14	13	14	0.23		
	19H	84	77.16	14	15	0.26		
	20H	88	81.18	14	15	0.29		
	21H	92	85.21	14	15	0.30		
	22H	96	89.24	14	15	0.35		
	23H	100	93.27	14	15	0.38		
	24H	104	97.30	14	15	0.40		
	25H	108	101.33	14	15	0.45		
	26H	112	105.36	14	15	0.49		
	27H	116	109.40	14	15	0.50		
	28H	120	113.43	14	15	0.56		
	29H	124	117.46	14	15	0.60		
	30H	128	121.50	14	15	0.63		