


QSC**QUICK SHAFT-LOCKING CLAMPS****IMAO**

Body / Handle	Locking Block	Flat Spring
Die cast zinc Chrome plated finish	Cast bronze (CAC402)	Stainless steel (SUS304)

Part Number	d	L ₂	L	W	H	R	L ₁	d ₁	W ₁	P	M	P ₁	P ₂
QSC10S	10	17	45	20	42	39	17.6	M4	15.5	30	M4×0.7 6 deep	20	18
QSC12S	12						18.8						
QSC14S	14						19.9						
QSC15L	15						24.1						
QSC16L	16	20	55	26	50	50	24.7	M5	20.5	35	M5×0.8 8 deep	20	20
QSC20L	20						27						

Part Number	Weight (g)	Shaft Dia. (h9)
QSC10S	228	φ 10
QSC12S	224	φ 12
QSC14S	220	φ 14
QSC15L	428	φ 15
QSC16L	418	φ 16
QSC20L	359	φ 20