





SUS40A

● Order No. Example



The KANA Standard SUS (Stainless Steel) A-type Sprocket can handle various environments due to its excellent corrosion resistance and durability. Stock established of tooth numbers for the very frequently used chain No.40 from 10T to 40T! Transformation to both single boss/double boss by boss welding!

- Chain No.40
- Chain Pitch (P)12.70mm
- Roller Link Inner Width (W) 7.95mm
- Roller Outside Diameter (Dr) 7.92mm
- Tooth Width (T) 7.2 mm

 Stainless Steel  304

| Type | No. of Teeth | Outer Diameter Do | Pitch Diameter Dp | Shaft Hole Diameter d | | Weight kg | ¥ | Semi-F ¥ |
|----------------|--------------|-------------------|-------------------|-----------------------|---------|-----------|---|----------|
| | | | | Prepared Hole Product | Minimum | | | |
| SUS 40A | 10 | 47 | 41.10 | 9 | 10 | 0.05 | | |
| | 11 | 51 | 45.08 | 10 | 11 | 0.09 | | |
| | 12 | 55 | 49.07 | 10 | 11 | 0.10 | | |
| | 13 | 59 | 53.07 | 12 | 13 | 0.12 | | |
| | 14 | 63 | 57.07 | 12 | 13 | 0.14 | | |
| | 15 | 67 | 61.08 | 12 | 13 | 0.16 | | |
| | 16 | 71 | 65.10 | 13 | 14 | 0.18 | | |
| | 17 | 76 | 69.12 | 13 | 14 | 0.20 | | |
| | 18 | 80 | 73.14 | 13 | 14 | 0.23 | | |
| | 19 | 84 | 77.16 | 14 | 15 | 0.26 | | |
| | 20 | 88 | 81.18 | 14 | 15 | 0.29 | | |
| | 21 | 92 | 85.21 | 14 | 15 | 0.30 | | |
| 22 | 96 | 89.24 | 14 | 15 | 0.35 | | | |
| 23 | 100 | 93.27 | 14 | 15 | 0.38 | | | |
| 24 | 104 | 97.30 | 14 | 15 | 0.40 | | | |