

SUSFBN25B

SUS FBN Finished Bore Sprocket


D10 K4x1.8 Specification

SUS FBN Finished Bore Sprocket

New JIS Keyway Specification





● Order No. Example

SUSFBN25B 17 D10



● Order No. Example

SUSFBN25B 17 D10 K4



- ChainNo.25
- Chain Pitch(P)6.35mm
- Bushing Link Inner Width(W)3.18mm
- Bushing Outside Diameter(Dr)3.30mm
- Tooth Width(T)2.8 mm

 Stainless Steel  SUS304

Shaft Hole Machined Specification

φD _{H7}	Keyway b×t ²	Set Screw M
10	3 x 1.4	4
12	4 x 1.8	5
15	5 x 2.3	6

★ Special Shaft Hole Machined Specification

φD _{H7}	Keyway b×t ²	Set Screw M
10	4 x 1.8	4

* Only the parts can be selected for special shaft hole machining. For your order method, please refer to the information below.

Type	No. of Teeth	φD _{H7}	Outer Diameter Do	Pitch Diameter Dp	Boss Diameter BD	Boss Length BL	a	Weight g	¥
SUS FBN 25B	16	10	36	32.55	21	16	6	60	
	17	10	38	34.56	23	16	6	70	
	18	10	40	36.57	25	16	6	70	
	19	10	12	42	38.58	26	16	6	80
	20	10	12	44	40.59	28	16	6	80
	21	12	15	46	42.61	30	18	7	90
	22	12	15	48	44.62	30	18	7	100
	23	12	15	50	46.63	30	18	7	110
	24	12	15	52	48.65	30	18	7	120
	25	12	15	54	50.66	30	18	7	140
26	12	15	56	52.68	30	18	7	140	
27	12	15	58	54.70	30	18	7	150	
28	12	15	60	56.71	30	18	7	150	
30	12	15	64	60.75	30	18	7	160	
32	12	15	68	64.78	30	18	7	200	



Sprocket No. φD_{H7} and Quantity



Same-day shipping

Postage



* Since we also manufacture sizes other than those in the catalog, and machine shaft holes/keys/taps, etc., depending on your request, please contact our company's sales office for details.



* If you order a special shaft diameter specification, please append K4 after the hole diameter.

Example: SUSFBN25B19D10K4