


NK40B



Order No. Example

NK40B 20



Ground Specification



Welded Specification

- Chain **No.40**
- Chain Pitch (P)**12.70mm**
- Roller Link Inner Width (W) **7.95mm**
- Roller Outside Diameter (Dr) **7.92mm**
- Tooth Width (T) **7.2 mm**

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d			Boss Diameter BD	Boss Length BL	Shape	Material	Weight kg	¥	Semi-F ¥
				Prepared Hole Product	Minimum	Maximum							
NK 40B	8	39	33.19	9	10	14	★24	22	Ground Specification	Carbon Structural Steel High-frequency Hardened Teeth	0.10		
	9	43	37.13	9	10	16	★28	22			0.11		
	10	47	41.10	9	10	18	★32	22			0.14		
	11	51	45.08	10	11	20	★36	22			0.19		
	12	55	49.07	10	11	22	★40	22			0.22		
	13	59	53.07	12	13	20	37	22			0.23		
	14	63	57.07	12	13	25	42	22			0.28		
	15	67	61.08	12	13	28	46	22			0.34		
	16	71	65.10	13	14	32	50	22			0.40		
	17	76	69.12	13	14	32	54	22			0.46		
	18	80	73.14	13	14	35	57	22			0.51		
	19	84	77.16	14	15	40	62	22			0.59		
	20	88	81.18	14	15	45	67	25			0.76		
	21	92	85.21	14	15	48	71	25			0.85		
	22	96	89.24	14	15	51	75	25			0.95		
	23	100	93.27	14	15	51	77	25			1.00		
	24	104	97.30	14	15	42	63	25			0.84		
	25	108	101.33	14	15	42	63	25			0.88		
	26	112	105.36	14	15	42	63	25			0.92		
	27	116	109.40	14	15	42	63	25			0.96		
28	120	113.43	14	15	42	63	25	1.00					
29	124	117.46	14	15	42	63	25	1.00					
30	128	121.50	14	15	42	63	25	1.10					
31	133	125.53	14	15	45	68	28	1.20					
32	137	129.57	14	15	45	68	28	1.30					
33	141	133.61	14	15	45	68	28	1.30					
34	145	137.64	14	15	45	68	28	1.30					
35	149	141.68	14	15	45	68	28	1.40					
36	153	145.72	16	17	45	68	28	1.50					
37	157	149.75	16	17	45	68	28	1.55					
38	161	153.79	16	17	45	68	28	1.60					
39	165	157.83	16	17	45	68	28	1.65					
40	169	161.87	16	17	45	68	28	1.70					