



Order No. Example

K40B 20



- Chain No.40
- Chain Pitch (P)12.70mm
- Roller Link Inner Width (W) 7.95mm
- Roller Outside Diameter (Dr) 7.92mm
- Tooth Width (T) 7.2 mm

m Carbon Structural Steel

h High-frequency Hardened Teeth

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d		Boss Diameter BD	Boss Length BL	Shape	Weight kg	¥	Semi-F ¥				
				Prepared Hole Product	Minimum							Maximum			
K 40B	10	47	41.10	9	10	16	28	25	Ground Specification						
	11	51	45.08	10	11	16	30	25							
	12	55	49.07	10	11	18	34	25							
	13	59	53.07	12	13	20	38	25							
	14	63	57.07	12	13	25	42	25							
	15	67	61.08	12	13	28	46	25							
	16	71	65.10	13	14	30	50	25							
	17	76	69.12	13	14	32	54	30							
	18	80	73.14	13	14	32	54	30							
	19	84	77.16	14	15	32	54	30							
	20	88	81.18	14	15	35	56	40							
	21	92	85.21	14	15	35	56	40							
	22	96	89.24	14	15	35	56	40							
	23	100	93.27	14	15	35	56	40							
	24	104	97.30	14	15	35	56	40							
	25	108	101.33	14	15	35	56	40							
	26	112	105.36	14	15	35	56	40							
	27	116	109.40	14	15	45	65	40							
	28	120	113.43	14	15	45	65	40							
	29	124	117.46	14	15	45	65	40							
	30	128	121.50	14	15	45	65	40							
	31	133	125.53	14	15	45	65	40							
	32	137	129.57	14	15	45	65	40							
	33	141	133.61	14	15	45	65	40							
	34	145	137.64	14	15	45	65	40							
	35	149	141.68	14	15	45	65	40							
	36	153	145.72	16	17	45	68	35							
	37	157	149.75	16	17	45	68	35							
	38	161	153.79	16	17	45	68	35							
	39	165	157.83	16	17	45	68	35							
	40	169	161.87	16	17	45	68	35							



Order Method

Sprocket No. and Quantity



Guide

* Since we also manufacture sizes other than those in the catalog, and machine shaft holes/keys/taps, etc., depending on your request, please contact our company's sales office for details.



Postage

Same-day shipping

* Please refer to P24 to P33 for the Semi-F Series <Complete Product> order method.