





# HG80A

## ● Order No. Example



- Chain .....No.80
- Chain Pitch .....(P)25.4 mm
- Roller Link Inner Width .....(W)15.88mm
- Roller Outside Diameter .....(Dr)15.88mm
- Tooth Width .....(T)14.6 mm

-  Carbon Structural Steel
-  High-frequency Hardened Teeth

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d		Weight kg	¥	Semi-F ¥
				Prepared Hole	Minimum			
HG 80A	10H	93	82.19	15	16	0.60		
	11H	102	90.16	15	16	0.73		
	12H	110	98.14	15	16	0.83		
	13H	118	106.14	16	17	1.00		
	14H	127	114.15	16	17	1.16		
	15H	135	122.17	20	21	1.30		
	16H	143	130.20	20	21	1.50		
	17H	151	138.23	20	21	1.70		
	18H	159	146.27	20	21	1.90		
	19H	167	154.32	20	21	2.10		
	20H	176	162.37	20	21	2.35		
	21H	184	170.42	20	21	2.57		
	22H	192	178.48	26	27	2.82		
	23H	200	186.54	26	27	3.10		
	24H	208	194.60	26	27	3.35		
	25H	216	202.66	26	27	3.65		
	26H	224	210.72	26	27	3.95		
	27H	233	218.79	26	27	4.25		
	28H	241	226.86	26	27	4.60		
	29H	249	234.93	26	27	4.93		
	30H	257	243.00	26	27	5.30		
	32H	273	259.14	26	27	6.00		
	34H	289	275.29	26	27	6.80		
	35H	297	283.36	26	27	7.20		
	36H	306	291.43	26	27	7.60		