



Order No. Example

K50B 15



- ChainNo.50
- Chain Pitch(P)15.875mm
- Roller Link Inner Width(W) 9.53 mm
- Roller Outside Diameter(Dr)10.16 mm
- Tooth Width(T) 8.7 mm

- m Carbon Structural Steel
- h High-frequency Hardened Teeth

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d		Boss Diameter BD	Boss Length BL	Shape	Weight kg	¥	Semi-F ¥
				Proposed Min Product	Minimum/Maximum						
K 50B	10	58	51.37	10	11 20	35	25	Ground Specification	0.25		
	11	64	56.35	12	13 20	37	25		0.30		
	12	69	61.34	12	13 25	43	25		0.40		
	13	74	66.34	12	13 28	48	30		0.50		
	14	79	71.34	12	13 32	53	30		0.60		
	15	84	76.35	12	13 35	58	30		0.70		
	16	89	81.37	14	15 42	63	30		0.80		
	17	94	86.39	14	15 45	65	40		0.95		
	18	100	91.42	14	15 45	65	40		1.20		
	19	105	96.45	14	15 45	65	40		1.30		
	20	110	101.48	14	15 46	70	45		1.60		
	21	115	106.51	14	15 46	70	45		1.75		
	22	120	111.55	16	17 46	70	45		1.80		
	23	125	116.58	16	17 46	70	45		1.85		
	24	130	121.62	16	17 46	70	45		1.90		
	25	135	126.66	16	17 46	70	45		2.00		
	26	140	131.70	16	17 46	70	45		2.10		
	27	145	136.74	16	17 46	70	45		2.20		
	28	150	141.79	16	17 46	70	45		2.35		
	29	155	146.83	16	17 46	70	45		2.50		
	30	161	151.87	16	17 46	70	45		2.60		
	31	166	156.92	16	17 46	70	45		2.70		
	32	171	161.96	16	17 46	70	45		2.90		
	33	176	167.01	16	17 46	70	45		2.95		
	34	181	172.05	16	17 46	70	45		3.00		
	35	186	177.10	16	17 46	70	45		3.10		



Order Method

Sprocket No. and Quantity



Guide

* Since we also manufacture sizes other than those in the catalog, and machine shaft holes/keys/taps, etc., depending on your request, please contact our company's sales office for details.



Postage

Same-day shipping

* Please refer to P24 to P33 for the Semi-F Series <Complete Product> order method.