



Order No. Example

50SD 15



- ChainNo.50
- Chain Pitch(P)15.875mm
- Roller Link Inner Width(W) 9.53 mm
- Roller Outside Diameter(Dr)10.16 mm
- Tooth Width(T) 8.7 mm (C)31.3mm

- m Carbon Structural Steel
- h High-frequency Hardened Teeth

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d			Boss Diameter BD	Boss Length BL	Weight kg	¥	Semi-F ¥
				Prepared Hole Product	Minimum	Maximum					
50 SD	10	58	51.37	13	14	18	32	40	0.40		
	11	64	56.35	13	14	20	37	40	0.52		
	12	69	61.34	13	14	25	43	40	0.63		
	13	74	66.34	13	14	28	48	40	0.75		
	14	79	71.34	13	14	32	53	40	0.90		
	15	84	76.35	13	14	35	58	40	1.04		
	16	89	81.37	13	14	42	63	40	1.22		
	17	94	86.39	13	14	45	68	40	1.41		
	18	100	91.42	13	14	48	73	40	1.61		
	19	105	96.45	16	17	52	79	40	1.80		
	20	110	101.48	16	17	57	84	40	1.95		
	21	115	106.51	16	17	60	89	40	2.27		
	22	120	111.55	16	17	62	92	40	2.46		
	23	125	116.59	16	17	68	99	40	2.77		
	24	130	121.62	16	17	70	102	40	2.98		
	25	135	126.66	16	17	75	109	40	3.32		
	26	140	131.70	18	19	78	115	40	3.66		
	27	145	136.74	18	19	82	120	40	3.97		
	28	150	141.79	18	19	85	125	40	4.29		
	29	155	146.83	18	19	90	130	40	4.62		
	30	161	151.87	18	19	96	136	40	5.00		



Sprocket No. and Quantity

Order Method



Guide

* Since we also manufacture sizes other than those in the catalog, and machine shaft holes/keys/taps, etc., depending on your request, please contact our company's sales office for details.



Same-day shipping

Postage

* Please refer to P24 to P33 for the Semi-F Series <Complete Product> order method.