


# NK50-2B



## ● Order No. Example

### NK50-2B 15



Ground Specification



Welded Specification

- Chain .....No.50-2
- Chain Pitch .....(P)15.875mm
- Roller Link Inner Width (W) 9.53 mm
- Roller Outside Diameter (Dr)10.16 mm
- Tooth Width .....(T) 8.4 mm (M)26.5mm

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d			Boss Diameter BD	Boss Length BL	Shape	Material	Weight kg	¥	Semi-F ¥
				Proposed Hole Product	Minimum	Maximum							
NK 50-2B	10	58	51.37	13	14	20	35	40	Ground Specification	High-Carbon Structural Steel High-frequency Hardened Teeth	0.50		
	11	64	56.35	13	14	22	40	40			0.50		
	12	69	61.34	13	14	25	42	40			0.62		
	13	74	66.34	13	14	30	49	40			0.75		
	14	79	71.34	13	14	32	54	40			0.90		
	15	84	76.35	13	14	38	59	40			1.10		
	16	89	81.37	13	14	42	64	45			1.40		
	17	94	86.39	13	14	45	68	45			1.60		
	18	100	91.42	13	14	48	74	45			1.80		
	19	105	96.45	16	17	55	79	45			2.10		
	20	110	101.48	16	17	57	84	45			2.30		
	21	115	106.51	16	17	60	89	45			2.60		
	22	120	111.55	16	17	63	94	50			3.00		
	23	125	116.58	16	17	66	99	50			3.50		
	24	130	121.62	16	17	70	105	50			3.80		
	25	135	126.66	16	17	70	105	50	4.20				
	26	140	131.70	18	19	70	105	50	Ground Specification	Carbon Structural Steel	4.50		
	27	145	136.74	18	19	70	105	50			4.80		
	28	150	141.79	18	19	75	110	50			5.10		
	29	155	146.83	18	19	75	110	50			5.50		
	30	161	151.87	18	19	80	120	50			5.80		