


100A

● Order No. Example

100A 20
 └───┬───┘
 Type No. of Teeth
 └───┬───┘
 Sprocket No.



- Chain No.100
- Chain Pitch (P)31.75mm
- Roller Link Inner Width (W)19.05mm
- Roller Outside Diameter (Dr)19.05mm
- Tooth Width (T)17.6 mm

 Common Steel

| Type | No. of Teeth | Outer Diameter Do | Pitch Diameter Dp | Shaft Hole Diameter d | | Weight kg | ¥ | Semi-F ¥ |
|------|--------------|----------------------|----------------------|-----------------------|---------|--------------|---|----------|
| | | | | Prepared Hole Product | Minimum | | | |
| 100A | 10 | 117 | 102.74 | 20 | 21 | 1.10 | | |
| | 11 | 127 | 112.70 | 20 | 21 | 1.30 | | |
| | 12 | 138 | 122.67 | 20 | 21 | 1.60 | | |
| | 13 | 148 | 132.67 | 20 | 21 | 1.90 | | |
| | 14 | 158 | 142.68 | 20 | 21 | 2.15 | | |
| | 15 | 168 | 152.71 | 20 | 21 | 2.50 | | |
| | 16 | 179 | 162.74 | 20 | 21 | 2.83 | | |
| | 17 | 189 | 172.79 | 20 | 21 | 3.20 | | |
| | 18 | 199 | 182.84 | 20 | 21 | 3.60 | | |
| | 19 | 209 | 192.90 | 20 | 21 | 4.00 | | |
| | 20 | 220 | 202.96 | 20 | 21 | 4.40 | | |
| | 21 | 230 | 213.03 | 20 | 21 | 4.90 | | |
| | 22 | 240 | 223.10 | 26 | 27 | 5.35 | | |
| | 23 | 250 | 233.17 | 26 | 27 | 5.80 | | |
| | 24 | 260 | 243.25 | 26 | 27 | 6.40 | | |
| | 25 | 270 | 253.32 | 26 | 27 | 6.90 | | |
| | 26 | 281 | 263.40 | 26 | 27 | 7.50 | | |
| | 27 | 291 | 273.49 | 26 | 27 | 8.10 | | |
| | 28 | 301 | 283.57 | 26 | 27 | 8.70 | | |
| | 29 | 311 | 293.66 | 26 | 27 | 9.30 | | |
| | 30 | 321 | 303.75 | 26 | 27 | 10.00 | | |
| | 31 | 331 | 313.83 | 26 | 27 | 10.63 | | |
| | 32 | 341 | 323.92 | 26 | 27 | 11.35 | | |
| | 33 | 352 | 334.01 | 26 | 27 | 12.00 | | |
| | 34 | 362 | 344.11 | 26 | 27 | 12.80 | | |