



# HG120A

## Order No. Example

### HG120A 20H



- Chain .....No.120
- Chain Pitch .....(P)38.10mm
- Roller Link Inner Width .....(W)25.40mm
- Roller Outside Diameter .....(Dr)22.23mm
- Tooth Width .....(T)23.5 mm

**m** Carbon Structural Steel

**h** High-frequency Hardened Teeth

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d		Weight kg	¥	Semi-F ¥
				Prepared Hole Product	Minimum			
HG 120A	10H	140	123.29	23	24	2.16		
	11H	153	135.24	25	26	2.60		
	12H	165	147.21	25	26	3.10		
	13H	177	159.20	25	26	3.60		
	14H	190	171.22	25	26	4.20		
	15H	202	183.25	25	26	4.80		
	16H	214	195.29	25	26	5.50		
	17H	227	207.35	25	26	6.20		
	18H	239	219.41	25	26	6.95		
	19H	251	231.48	25	26	7.70		
	20H	263	243.55	25	26	8.55		
	21H	276	255.63	25	26	9.40		
	22H	288	267.72	26	27	10.30		
	23H	300	279.80	26	27	11.30		
	24H	312	291.90	26	27	12.30		
	25H	324	303.99	26	27	13.30		
	26H	337	316.09	26	27	14.40		
	27H	349	328.19	26	27	15.50		
	28H	361	340.29	26	27	16.70		
29H	373	352.39	26	27	17.80			
30H	385	364.50	26	27	19.20			
32H	410	388.71	30	31	21.80			
34H	434	412.93	30	31	24.60			
35H	446	425.04	30	31	26.10			
36H	458	437.15	30	31	27.60			