


2042B




Standard Double Pitch Sprocket for R Rollers B-type

Order No. Example


2042B 20



Ground Specification Welded Specification



Ground Specification



Welded Specification

- Chain No.C2042
- Chain Pitch (P)25.4 mm
- Roller Link Inner Width (W) 7.95mm
- Roller Outside Diameter (Dr)15.88mm
- Tooth Width (T) 7.2 mm

Type	Action No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d			Boss Diameter BD	Boss Length BL	Shape	Material	Weight kg	¥	Semi-F ¥
				Prepared Holes	Minimum	Maximum							
2042B	7	68	58.54	14	15	22	★40	25	Ground Specification	Carbon Structural Steel	0.26		
	8	77	66.37	14	15	28	★48	25			0.37		
	9	85	74.26	14	15	32	52	25			0.47		
	10	93	82.20	15	16	42	63	25			0.70		
	11	102	90.16	15	16	42	63	25			0.77		
	12	108	98.14	15	16	42	63	25			0.84		
	13	118	106.14	16	17	42	63	25			0.97		
	14	127	114.15	16	17	42	63	25			1.07		
	15	135	122.17	20	21	45	68	28			1.26		
	16	143	130.20	20	21	45	68	28			1.30		
	17	151	138.23	20	21	45	68	28			1.35		
	18	159	146.27	20	21	45	68	28			1.45		
	19	167	154.32	20	21	45	68	28			1.60		
	20	176	162.37	20	21	45	68	28			1.80		
	21	183	170.42	20	21	48	73	32			1.91		
22	192	178.48	26	27	48	73	32	2.03					
23	200	186.54	26	27	48	73	32	2.15					
24	208	194.60	26	27	48	73	32	2.28					
25	216	202.66	26	27	48	73	32	2.42					
26	224	210.72	26	27	48	73	32	2.56					
28	241	226.86	26	27	48	73	32	2.87					
30	257	243.00	26	27	48	73	32	3.19					
32	273	259.14	26	27	55	83	32	4.04					

Sprocket No. and Quantity



* Since we also manufacture sizes other than those in the catalog, and machine shaft holes/keys/taps, etc., depending on your request, please contact our company's sales office for details.

! Sprockets with a ★ symbol for BD have a channel in the boss exterior.

No. of Teeth	S	GD
7		35
8	6	43

Same-day shipping

* Please refer to P24 to P33 for the Semi-F Series <Complete Product> order method.