



SUS60A

● Order No. Example

SUS60A 20



- Chain No.60
- Chain Pitch (P)19.05mm
- Bushing Link Inner Width (W)12.70mm
- Bushing Outside Diameter (Dr)11.91mm
- Tooth Width (T)11.7 mm

 Stainless Steel  304

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d		Weight kg	¥	Semi-F ¥
				Prepared Hole Product	Minimum			
SUS 60A	10	70	61.65	14	15	0.27		
	11	76	67.62	14	15	0.30		
	12	83	73.60	14	15	0.38		
	13	89	79.60	14	15	0.45		
	14	95	85.61	16	17	0.50		
	15	101	91.62	16	17	0.60		
	16	107	97.65	16	17	0.65		
	17	113	103.67	16	17	0.75		
	18	119	109.71	16	17	0.84		
	19	126	115.74	16	17	0.93		
	20	132	121.78	16	17	1.05		
	21	138	127.82	16	17	1.15		
	22	144	133.86	16	17	1.25		
	23	150	139.90	16	17	1.40		
	24	156	145.95	18	19	1.50		
	25	162	151.99	18	19	1.62		
	26	168	158.04	18	19	1.78		
	27	174	164.09	18	19	1.90		
	28	180	170.14	18	19	2.05		
	29	187	176.20	18	19	2.20		