



NK60B



● Order No. Example

NK60B 20



- Chain No.60 Ground Specification Welded Specification
- Chain Pitch (P)19.05mm
- Roller Link Inner Width (W)12.70mm
- Roller Outside Diameter (Dr)11.91mm
- Tooth Width (T)11.7 mm

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d			Boss Diameter BD	Boss Length BL	Shape	Material	Weight kg	¥	Semi-F ¥
				Prepared Hole Product	Minimum	Maximum							
NK 60B	8	58	49.78	12	13	20	★34	32	Ground Specification	High-frequency Hardened Teeth	0.30		
	9	64	55.70	12	13	25	★43	32			0.40		
	10	70	61.65	14	15	30	★49	32			0.49		
	11	76	67.62	14	15	32	★51	32			0.60		
	12	83	73.60	14	15	32	51	32			0.69		
	13	89	79.60	14	15	35	57	32			0.81		
	14	95	85.61	16	17	40	62	32			0.96		
	15	101	91.62	16	17	45	68	32			1.10		
	16	107	97.65	16	17	48	73	32			1.30		
	17	113	103.67	16	17	48	73	32			1.40		
	18	119	109.71	16	17	55	83	40			2.00		
	19	126	115.74	16	17	55	83	40			2.10		
	20	132	121.78	16	17	55	83	40	2.20				
	21	138	127.82	16	17	55	83	40	2.30				
	22	144	133.86	16	17	55	83	40	2.50				
	23	150	139.90	16	17	55	83	40	2.50				
	24	156	145.95	18	19	55	83	40	2.60				
	25	162	151.99	18	19	55	83	40	2.70				
	26	168	158.04	18	19	55	83	40	2.90				
	27	174	164.09	18	19	55	83	40	3.00				
	28	180	170.14	18	19	55	83	40	3.10				
	29	187	176.20	18	19	55	83	40	3.30				
	30	193	182.25	18	19	55	83	40	3.40				
	31	199	188.30	20	21	55	83	40	Ground Specification	Common Steel	3.64		
	32	205	194.35	20	21	55	83	40			3.80		
	33	211	200.41	20	21	55	83	40			4.00		
	34	217	206.46	20	21	55	83	40			4.15		
	35	223	212.52	20	21	55	83	40			4.33		
	36	229	218.57	20	21	55	83	40			4.52		
	37	235	224.63	20	21	55	83	40			4.70		
38	241	230.69	20	21	55	83	40	4.90					
39	247	236.74	20	21	55	83	40	5.10					
40	253	242.80	20	21	55	83	40	5.30					