



Order No. Example



- Chain No.60
- Chain Pitch (P)19.05mm
- Roller Link Inner Width (W)12.70mm
- Roller Outside Diameter (Dr)11.91 mm
- Tooth Width (T)11.7 mm (C)38.3mm

- m Carbon Structural Steel
- h High-frequency Hardened Teeth

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d			Boss Diameter		Boss Length BL	Weight kg	¥	Semi-F ¥
				Prepared Hole Product	Minimum	Maximum	BD	BL				
60SD	10	70	61.65	13	14	20	37	50	0.74			
	11	76	67.62	13	14	26	45	50	0.92			
	12	83	73.60	13	14	32	51	50	1.14			
	13	89	79.60	16	17	35	57	50	1.39			
	14	95	85.61	16	17	42	64	50	1.63			
	15	101	91.62	16	17	46	70	50	1.96			
	16	107	97.65	16	17	51	76	50	2.20			
	17	113	103.67	16	17	55	82	50	2.56			
	18	119	109.71	18	19	60	88	50	2.90			
	19	126	115.74	18	19	63	94	50	3.26			
	20	132	121.78	18	19	68	100	50	3.70			
	21	138	127.82	18	19	75	107	50	4.13			
	22	144	133.86	18	19	78	113	50	4.59			
	23	150	139.90	20	21	82	119	50	5.03			
	24	156	145.95	20	21	85	125	50	5.52			
	25	162	151.99	20	21	90	130	50	5.99			
	26	168	158.04	20	21	96	138	50	6.64			
	27	174	164.09	20	21	100	144	50	7.20			
	28	180	170.14	20	21	106	150	50	7.78			
	29	187	176.20	20	21	110	157	50	8.43			
	30	193	182.25	20	21	114	163	50	9.06			



Sprocket No. and Quantity



* Since we also manufacture sizes other than those in the catalog, and machine shaft holes/keys/taps, etc., depending on your request, please contact our company's sales office for details.



Same-day shipping

* Please refer to P24 to P33 for the Semi-F Series <Complete Product> order method.