



H05V-K <HAR>

European <HAR> cable type certification

Info

- <HAR>



Benefits

- Cables' <HAR>marking also stands for the international endorsement of national certification institutes' testing marks and certificates, e. g. <VDE><HAR>. The <HAR>marking is of special importance in case of goods traffic between European countries.

Application range

- Internal wiring of devices
- Protected installation in and on lighting equipments
- Signal systems in and on plaster in tubes

Product features

- Flame-retardant according IEC 60332-1-2
- Spool: d1 = 18 mm; d2 = 200 mm; b = 85 mm

Norm references / Approvals

- <HAR> cable type certification acc. EN 50525-2-31

Product Make-up

- Fine-wired copper conductor of bare copper strands in line with conductor class 5 acc. IEC 60228
- Core insulation: Based on PVC

Technical data

Classification
ETIM 5.0 Class-ID: EC000993
ETIM 5.0 Class-Description: Single core cable

Conductor stranding
Fine wire according to VDE 0295 Class 5/ IEC 60228 Class 5

Minimum bending radius
According to EN 50565-1
4 x outer diameter (OD) for normal use; 2 x OD for cautions bending

Nominal voltage
U₀/U: 300/500 V

Test voltage
2000 V

Current rating
VDE 0298 Part 4
EN 50565-1/ VDE 0298-565-1

Temperature range
Fixed installation: -40°C to +80°C
Moved: +5°C to +70°C

Conductor cross-section (mm ²)	Outer diameter (mm)	m/ring	m/spool	Copper index (kg/km)	Weight (kg/km)	brown	black	grey	blue	green/yellow
0.5	2.1 - 2.5	100		4.8	9	4510031	4510011	4510061	4510021	4510001
0.75	2.2 - 2.7	100		7.2	12	4510032	4510012	4510062	4510022	4510002
1	2.4 - 2.8	100		9.6	15	4510033	4510013	4510063	4510023	4510003
0.5	2.1 - 2.5		250	4.8	9	4510031S	4510011S	4510061S	4510021S	4510001S
0.75	2.2 - 2.7		250	7.2	12	4510032S	4510012S	4510062S	4510022S	4510002S
1	2.4 - 2.8		250	9.6	15	4510033S	4510013S	4510063S	4510023S	4510003S

Conductor cross-section (mm ²)	Outer diameter (mm)	m/ring	m/spool	Copper index (kg/km)	Weight (kg/km)	orange	dark blue	white	green	yellow
0.5	2.1 - 2.5	100		4.8	9	4510091	4510141	4510051	4510121	4510111
0.75	2.2 - 2.7	100		7.2	12	4510092	4510142	4510052	4510122	4510112
1	2.4 - 2.8	100		9.6	15	4510093	4510143	4510053	4510123	4510113
0.5	2.1 - 2.5		250	4.8	9	4510091S	4510141S	4510051S	4510121S	4510111S
0.75	2.2 - 2.7		250	7.2	12	4510092S	4510142S	4510052S	4510122S	4510112S
1	2.4 - 2.8		250	9.6	15	4510093S	4510143S	4510053S	4510123S	

Conductor cross-section (mm ²)	Outer diameter (mm)	m/ring	m/spool	Copper index (kg/km)	Weight (kg/km)	violet	red	ultra-marine blue	Dark blue/white	transparent
0.5	2.1 - 2.5	100		4.8	9	4510071	4510041	4510161	4510921	
0.75	2.2 - 2.7	100		7.2	12	4510072	4510042		4510922	
1	2.4 - 2.8	100		9.6	15	4510073	4510043	4510163	4510923	
0.5	2.1 - 2.5		250	4.8	9	4510071S	4510041S			
0.75	2.2 - 2.7		250	7.2	12	4510072S	4510042S	4510162S		4510102S
1	2.4 - 2.8		250	9.6	15	4510073S	4510043S	4510163S		4510103S

Conductor cross-section (mm ²)	Outer diameter (mm)	m/ring	m/spool	Copper index (kg/km)	Weight (kg/km)	pink
0.5	2.1 - 2.5	100		4.8	9	4510081
0.75	2.2 - 2.7	100		7.2	12	4510082
1	2.4 - 2.8	100		9.6	15	4510083
0.75	2.2 - 2.7		250	7.2	12	4510082S

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request. Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges. Photographs are not to scale and do not represent detailed images of the respective products. The outer diameters stated in the part number table are maximum values.