



# SUS80B



## SUS Stainless Steel Sprocket B-type

### Order No. Example

**SUS 80B 20**



- Chain .....No.80
- Chain Pitch .....(P)25.4 mm
- Roller Link Inner Width .....(W)15.88mm
- Roller Outside Diameter .....(Dr)15.88mm
- Tooth Width .....(T)14.6 mm

Ground Specification

Welded Specification

m Stainless Steel GB304

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d			Boss Diameter BD	Boss Length BL	Shape	Weight kg	¥	Semi-F ¥
				Prepared Hole Product	Minimum	Maximum						
SUS 80B	10	93	82.19	15	16	32	52	40	Ground Specification	1.02		
	11	102	90.15	15	16	38	60	40		1.25		
	12	110	98.14	15	16	45	67	40		1.60		
	13	118	106.14	16	17	51	77	40		1.90		
	14	127	114.15	16	17	51	77	40		2.15		
	15	135	122.17	20	21	63	93	40		2.30		
	16	143	130.20	20	21	63	93	40		2.50		
	17	151	138.23	20	21	63	93	40		2.95		
	18	159	146.27	20	21	63	93	40		3.15		
	19	167	154.32	20	21	63	93	40		3.40		
	20	176	162.37	20	21	63	93	40	3.60			
	21	184	170.42	20	21	63	93	40	3.85			
	22	192	178.48	26	27	63	93	45	Welded Specification	5.00		
	23	200	186.54	26	27	63	93	45		5.23		
	24	208	194.60	26	27	63	93	45		5.50		
	25	216	202.66	26	27	63	93	45		5.80		
	26	224	210.72	26	27	63	93	45		6.10		
	27	233	218.79	26	27	63	93	45		6.40		
	28	241	226.86	26	27	63	93	45		6.75		
	30	257	243.00	26	27	63	93	45		7.40		
32	273	259.14	26	27	63	93	45	8.15				
34	289	275.29	26	27	63	93	45	8.90				
35	297	283.36	26	27	63	93	45	9.30				
40	338	323.74	26	27	75	107	50	12.40				



Sprocket No. and Quantity



\* Since we also manufacture sizes other than those in the catalog, and machine shaft holes/keys/taps, etc., depending on your request, please contact our company's sales office for details.



Same-day shipping

\* Please refer to P24 to P33 for the Semi-F Series <Complete Product> order method.