


120A

● Order No. Example

120A 20
 └───┬───┘
 Type No. of Teeth
 └──────────┘
 Sprocket No.



- ChainNo.120
- Chain Pitch(P)38.10mm
- Roller Link Inner Width(W)25.40mm
- Roller Outside Diameter(Dr)22.23mm
- Tooth Width(T)23.5 mm

 Common Steel

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d		Weight kg	¥	Semi-F ¥
				Prepared Hole Product	Minimum			
120A	10	140	123.29	23	24	2.16		
	11	153	135.24	25	26	2.60		
	12	165	147.21	25	26	3.10		
	13	177	159.20	25	26	3.60		
	14	190	171.22	25	26	4.20		
	15	202	183.25	25	26	4.80		
	16	214	195.29	25	26	5.50		
	17	227	207.35	25	26	6.20		
	18	239	219.41	25	26	6.95		
	19	251	231.48	25	26	7.70		
	20	263	243.55	25	26	8.55		
	21	276	255.63	25	26	9.40		
	22	288	267.72	26	27	10.30		
	23	300	279.80	26	27	11.30		
	24	312	291.90	26	27	12.30		
	25	324	303.99	26	27	13.30		
	26	337	316.09	26	27	14.40		
	27	349	328.19	26	27	15.50		
	28	361	340.29	26	27	16.70		
	29	373	352.39	26	27	17.80		
	30	385	364.50	26	27	19.20		
	31	398	376.60	30	31	20.40		
	32	410	388.71	30	31	21.80		
	33	422	400.82	30	31	23.20		
	34	434	412.93	30	31	24.60		