




SKINDICHT® RWV-M without E+D



Benefits

- Combination of different conduit glands is possible
- Space- and weight-saving application due to thin cable diameters
- Decrease in installation height
- Cable runs parallel to the housing wall
- Corrosion-resistant

Application range

- Angled glands are used in areas where cables have to run in parallel to the housing wall.
- Electric motor manufacturing
- Machine and equipment manufacturing
- Plant engineering
- Light and sound applications

Product Make-up

- Metric connection thread acc. to DIN EN 60423
- Basis for technical information EN 50262

Note

- The protection class is dependent on the combination with the various special glands. The minimum standard is IP 55.
- Counter nut to be used: SKINDICHT® SM-M
- Cable glands are not included in scope of delivery

Technical data



Classification

ETIM 5.0 Class-ID: EC000441
ETIM 5.0 Class-Description:
Cable screw gland



Material

Body: zinc die-casting
Hexagon nut: nickel-plated brass
O-ring: NBR



Protection rating

IP 55



Temperature range

-20°C to +100°C

Article number	Article designation / size	B in mm	Thread length, D (mm)	K	L	Ø G	SW 1	Ø A 1	SW 2	Ø A 2	Pieces / PU
SKINDICHT® RWV-M without E+D											
52107801	12 x 1,5	21	11.5	5	21	8	14	16	17	18.9	25
52107811	16 x 1,5	23	11.5	5	24	12	18	20	22	24.5	25
52107821	20 x 1,5	28.5	12.5	5	29	15	22	24	27	30.1	25
52107831	25 x 1,5	30	13.5	5	31	20	27	29	32	35.7	10
52107841	32 x 1,5	33.5	13.5	5	33	27	34	33.5	41	45.6	10
52107851	40 x 1,5	43	15.5	5	43	35	42	43	46	50.6	5

Photographs are not to scale and do not represent detailed images of the respective products.



SKINDICHT® SE-M



Benefits

- Sealed by incised sealing ring
- Corrosion-resistant
- Easy to install
- Completely safe cable entry
- Low overall height

Application range

- For high mechanical stress
- When no connection thread is provided

Product Make-up

- M20 x 1.5 - M25 x 1.5 with 2 screw holes
- M32 x 1.5 with 4 screw holes
- With incised sealing ring

Technical data



Classification

ETIM 5.0 Class-ID: EC000441
ETIM 5.0 Class-Description:
Cable screw gland



Material

Body: zinc die-casting, grey, hammer tone finish
Compression screw: nickel-plated brass
Incised sealing ring: CR/NBR
O-ring: NBR



Protection rating

IP 55



Temperature range

-20°C to +80°C

Note

- Drawing on request

Article number	Article designation / size	Incised sealing ring ØF (mm)	Overall height (mm)	SW wrench size mm	Overall length, C (mm)	Overall width (mm)	Pieces / PU
SKINDICHT® SE-M							
52108000	M 20 x 1,5	4/7/10/13	31	20	49.2	42	10
52108010	M 25 x 1,5	8.5/11.5/14.5/17.5	40	25	68.2	60	5
52108020	M 32 x 1,5	16/19/22/25	51.5	32	84.2	66	1

Photographs are not to scale and do not represent detailed images of the respective products.