



# SUS2060B



## SUS Standard Stainless Steel Double Pitch Sprocket for S Rollers B-type

### ● Order No. Example

**SUS 2060B 9 1/2**



- Chain ..... No.C2060H
- Chain Pitch ..... (P)38.10mm
- Roller Link Inner Width ..... (W)12.70mm
- Roller Outside Diameter ..... (Dr)11.91mm
- Tooth Width ..... (T)11.7 mm

**m** Stainless Steel **GB** 304

Type	Action No. of Teeth	Actual No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d			Boss Diameter BD	Boss Length BL	Shape	Weight kg	¥	Semi-F ¥
					Prepared Holes	Minimum	Maximum						
<b>SUS 2060B</b>	9 1/2	19	126	117.34	16	17	55	83	40	Ground Specification	2.1		
	10 1/2	21	138	129.26	16	17	55	83	40		2.3		
	11 1/2	23	150	141.22	16	17	55	80	45		2.7		
	12 1/2	25	162	153.20	18	19	55	80	45		3.0		

\* Please refer to P24 to P33 for the Semi-F Series <Complete Product> order method.



Sprocket No. and Quantity

Order Method



Same-day shipping

Postage



Guide

\* Since we also manufacture sizes other than those in the catalog, and machine shaft holes/keys/taps, etc., depending on your request, please contact our company's sales office for details.