




SKINDICHT® MR-M hexagonal



Benefits

- Enables the use of cable glands with smaller connection threads than the existing threaded holes
- With guide notch for O-ring
- Assembling with a wrench

Application range

- Machines
- Devices
- Housings

Product Make-up

- Metric connection thread acc. to DIN EN 60423
- Basis for technical information EN 50262

Technical data



Classification

ETIM 5.0 Class-ID: EC000441
ETIM 5.0 Class-Description:
Cable screw gland



On request

VITON® O-ring
-20 °C to +200 °C



Material

Body: nickel-plated brass
O-ring: NBR



Temperature range

-30 °C to +100 °C

Article number	Thread, male M1	Thread, female M2	SW wrench size mm	Buiten ø (mm)	Overall length, C (mm)	Thread length, D (mm)	Outer Ø (mm)	Pieces / PU
SKINDICHT® MR-M hexagon								
52101965	16 x 1.5	12 x 1.5	18	20.2	8.5	5.5		50
52101966	20 x 1.5	16 x 1.5	22	24.4	9.0	6		50
52101967	25 x 1.5	16 x 1.5	28	31.2	10.0	6.5		50
52101968	25 x 1.5	20 x 1.5	28	31.2	10.0	6.5		50
52101969	32 x 1.5	16 x 1.5	36	40.0	11.5	8		25
52101972	32 x 1.5	20 x 1.5	36	40.0	11.5	8		25
52101973	32 x 1.5	25 x 1.5	36	40.0	11.5	8		25
52101974	40 x 1.5	25 x 1.5	43	47.5	12.5	8.5		10
52101975	40 x 1.5	32 x 1.5	43	47.5	12.5	8.5		10
52101976	50 x 1.5	40 x 1.5	54	58.0	14.0	10		5
52101977	63 x 1.5	50 x 1.5	67	74.0	14.0	9.5		5
52101979	75 x 1.5	63 x 1.5	80	90.0	17.0	11		1
SKINDICHT® MR-M, blank brass, with hexagon								
52006572	80 x 2	63 x 1.5	85		23.0	15	93.5	1

Viton® is a registered trademark of DuPont de Nemours

Photographs are not to scale and do not represent detailed images of the respective products.