



## H05RR-F

Rubber cable for light mechanical stress and handheld devices used in households, kitchens, offices

**Info**

- Light mechanical stress



### Benefits

- Type-compliant versions <HAR>-certified with “<HAR>” testing and certification mark for accelerated granting of approvals if final application of cable is within the European CENELEC area

### Application range

- Handheld and power supply devices according to EN 50565-2
- For lightweight workshop tools that are subject to light loads
- According to EN 50565-2: dry and damp rooms; only temporary use outdoors; not for industrial/commercial or agricultural facilities, except tailors/cutting workshops; not suitable for supplying industrial power tools
- Light & sound technology

### Product features

- Ozone-resistant

### Norm references / Approvals

- <HAR> cable type approval according to EN 50525-2-21

### Product Make-up

- Bare copper wire according to HAR
- Core insulation: rubber compound, type EI 4
- Outer sheath: rubber compound, type EM3

### Technical data

- Classification**  
ETIM 5.0 Class-ID: EC001578  
ETIM 5.0 Class-Description: Flexible cable
- Core identification code**  
Coloured according to HD 308
- Conductor stranding**  
Fine wire according to VDE 0295 Class 5/ IEC 60228 Class 5
- Minimum bending radius**  
4 to 8 x outer diameter (EN 50565-1)
- Nominal voltage**  
U<sub>0</sub>/U: 300/500 V
- Test voltage**  
2000 V
- Protective conductor**  
G = with GN-YE protective conductor  
X = without protective conductor
- Current rating**  
According to IEC 60364-5-52/  
VDE 0298-4  
EN 50565-1/ VDE 0298-565-1
- Temperature range**  
Flexible use: -25°C to +60°C

Article number	Number of cores and mm <sup>2</sup> per conductor	Outer diameter (mm)	Copper index (kg/km)	Weight (kg/km)
<b>H05RR-F</b>				
1600203	2 X 0.75	5.7 - 7.4	14.4	61
1600207	3 G 0.75	6.2 - 8.1	21.6	75
1600204	2 X 1.0	6.1 - 8.0	19.2	73
1600208	3 G 1.0	6.5 - 8.5	28.8	86
16002113	4 G 1.0	7.1 - 9.3	38.4	105
1600205	2 X 1.5	7.6 - 9.8	28.8	115
1600200	3 G 1.5	8.0 - 10.4	43.2	135
16002013	4 G 1.5	9.0 - 11.6	57.6	165
16002023	5 G 1.5	9.8 - 12.7	72	190
1600206	2 X 2.5	9.0 - 11.6	48	160
1600209	3 G 2.5	9.6 - 12.4	72	190
16002123	4 G 2.5	10.7 - 13.8	96	235
16002133	5 G 2.5	11.9 - 15.3	120	285

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request. Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges. Please find our standard lengths at: [www.lappkabel.de/en/cable-standardlengths](http://www.lappkabel.de/en/cable-standardlengths)  
Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum  
Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).  
Photographs are not to scale and do not represent detailed images of the respective products.

### Similar products

- H05RN-F refer to page 90