



Info

- CAN = Controller Area Network

Application range

UNITRONIC® BUS CAN

- Fixed installation

UNITRONIC® BUS CAN FD P

- For highly flexible applications

Product features

UNITRONIC® BUS CAN

- Maximum bit rate: 1 Mbit/s for 40 m segment length
- Larger conductor cross-section is necessary with increasing length. Refer to the table below (reference values from ISO 11898).
- ISO 11898 makes recommendations for the segment length, cable cross section and bit rate
- Flame-retardant according IEC 60332-1-2

UNITRONIC® BUS CAN FD P

- Halogen-free outer sheath
- Maximum bit rate: 1 Mbit/s for 40 m segment length
- Larger conductor cross-section is necessary with increasing length. Refer to the table below (reference values from ISO 11898).
- ISO 11898 makes recommendations for the segment length, cable cross section and bit rate
- Flame-retardant according IEC 60332-1-2

LAPP KABEL STUÏGART UNITRONIC® BUS CAN

Norm references / Approvals

- Standardised internationally in ISO 11898
- UL/CSA type CMX (UL 444)

Product Make-up

UNITRONIC® BUS CAN

- 0.22 + 0.34 + 0.5: bare stranded conductor, 7-wire
- 0.75: bare stranded conductor, fine-wire
- Colour-coded in accordance with DIN 47100
- Copper braid
- PVC sheath
- Colour: violet (RAL 4001)

UNITRONIC® BUS CAN FD P

- Stranded bare conductor
- Screening: wrapped with braided copper wires
- PUR outer sheath
- Colour: violet (RAL 4001)
- UV-resistant (but colour may change after some time)

Suitable connectors

UNITRONIC® BUS CAN

- EPIC® DATA CAN Sub-D Page 362
- EPIC® DATA CAN Sub-D PRO Page 363

UNITRONIC® BUS CAN

UNITRONIC® BUS CAN FD P

LAPP KABEL STUÏGART UNITRONIC® BUS CAN FD P

Technical data

- ETIM** ETIM 5.0 Class-ID: EC000830
ETIM 5.0 Class-Description: Data cable
- Mutual capacitance**
UNITRONIC® BUS CAN (800 Hz): max. 40 nF/km
UNITRONIC® BUS CAN FD P (800 Hz): max. 60 nF/km
- Peak operating voltage**
UNITRONIC® BUS CAN (not for power applications) 250 V
UNITRONIC® BUS CAN FD P 250 V (not for power transmission)
- Conductor resistance**
UNITRONIC® BUS CAN (loop): max. 186 ohm/km
UNITRONIC® BUS CAN FD P (loop): max. 159.8 ohm/km
- Minimum bending radius**
UNITRONIC® BUS CAN Fixed installation: 8 x outer diameter
UNITRONIC® BUS CAN FD P Flexing: 15 x outer diameter
- Test voltage** Core/core: 1500 V rms
- Characteristic impedance** 120 ohm
- Temperature range**
UNITRONIC® BUS CAN Fixed installation: -30°C to +80°C
Flexing: -5°C to +70°C
UNITRONIC® BUS CAN FD P Fixed installation: -40°C to +80°C
Flexing: -30°C to +70°C

Article number	Article designation	Number of pairs/ conductor cross section (mm ²)	Outer diameter (mm)	Conductor resistance	Copper index (kg/km)	Weight (kg/km)
for fixed installation						
2170260	UNITRONIC® BUS CAN	1 x 2 x 0,22	5.7	186	16.7	42
2170261	UNITRONIC® BUS CAN	2 x 2 x 0,22	7.6	186	34.8	68
2170263	UNITRONIC® BUS CAN	1 x 2 x 0,34	6.8	115	25	55
2170264	UNITRONIC® BUS CAN	2 x 2 x 0,34	8.5	115	46.4	88
2170266	UNITRONIC® BUS CAN	1 x 2 x 0,5	7.5	78	41.6	90
2170267	UNITRONIC® BUS CAN	2 x 2 x 0,5	9.6	78	59.4	106
2170269	UNITRONIC® BUS CAN	1 x 2 x 0,75	8.7	52	52.7	108
2170270	UNITRONIC® BUS CAN	2 x 2 x 0,75	11.5	52	80.6	142
For highly flexible applications (power chains, moving machine parts)						
2170272	UNITRONIC® BUS CAN FD P	1 x 2 x 0,25	6.4	159.8	24	40
2170273	UNITRONIC® BUS CAN FD P	2 x 2 x 0,25	8.4	159.8	33	65
2170275	UNITRONIC® BUS CAN FD P	1 x 2 x 0,34	6.8	122	32.8	60
2170276	UNITRONIC® BUS CAN FD P	2 x 2 x 0,34	9.6	122	52.4	88
2170278	UNITRONIC® BUS CAN FD P	1 x 2 x 0,5	8	72.8	41.9	74
2170279	UNITRONIC® BUS CAN FD P	2 x 2 x 0,5	10.8	72.8	59.4	100

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.
Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.
Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths
Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum
Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).
Photographs are not to scale and do not represent detailed images of the respective products.

Accessories

UNITRONIC® BUS CAN

- Multipurpose shears A and B refer to page 998
- SMART STRIP stripping tool
- SENSOR STRIP stripping tool refer to page 1003