



RoHS対応


ERON®

No.E-400S

STAINLESS STUD BOLTS

スタッドボルト(SUS)

材質 SUS316



仕様・価格表

1本価格

オーダーNo.	No.	A(並目)	B	C	D	質量g	価格
38819	BM04025S	M 4×0.7	25	12	7	1	1,620
38820	BM04035S	M 4×0.7	35	12	7	5	1,690
38821	BM04040S	M 4×0.7	40	20	7	5	1,680
38822	BM04045S	M 4×0.7	45	20	7	5	1,930
38823	BM04050S	M 4×0.7	50	20	7	6	1,890
38824	BM05025S	M 5×0.8	25	12	8	2	1,620
38825	BM05030S	M 5×0.8	30	12	8	4	1,620
38827	BM05040S	M 5×0.8	40	20	8	6	1,790
38828	BM05045S	M 5×0.8	45	20	8	6	1,930
38829	BM05050S	M 5×0.8	50	20	8	7	2,030
38830	BM06030S	M 6×1.0	30	13	9	5	1,620
38831	BM06035S	M 6×1.0	35	13	9	5	1,720
38832	BM06040S	M 6×1.0	40	25	9	5	1,790
38833	BM06045S	M 6×1.0	45	25	9	10	1,930
38834	BM06050S	M 6×1.0	50	25	9	10	2,030
38835	BM06060S	M 6×1.0	60	25	9	10	2,230
38836	BM06070S	M 6×1.0	70	25	9	15	2,480
38837	BM08040S	M 8×1.25	40	25	11	15	1,740
38838	BM08045S	M 8×1.25	45	25	11	16	2,000
38839	BM08050S	M 8×1.25	50	30	11	18	2,230
38840	BM08060S	M 8×1.25	60	30	11	20	2,450
38841	BM08070S	M 8×1.25	70	30	11	25	2,730
38842	BM08080S	M 8×1.25	80	30	11	30	3,050
38843	BM08090S	M 8×1.25	90	30	11	35	3,300
38844	BM08100S	M 8×1.25	100	30	11	40	3,630
38845	BM10050S	M10×1.5	50	30	13	30	2,450
38846	BM10060S	M10×1.5	60	30	13	35	2,840
38847	BM10070S	M10×1.5	70	30	13	40	3,190
38848	BM10080S	M10×1.5	80	40	13	45	3,430
38849	BM10090S	M10×1.5	90	40	13	50	3,750
38850	BM10100S	M10×1.5	100	40	13	55	4,030
38851	BM10125S	M10×1.5	125	40	13	70	4,750
38852	BM12060S	M12×1.75	60	40	15	40	2,870
38853	BM12070S	M12×1.75	70	40	15	50	3,430
38854	BM12080S	M12×1.75	80	40	15	60	3,430
38855	BM12090S	M12×1.75	90	40	15	70	3,580
38856	BM12100S	M12×1.75	100	65	15	80	4,370
38857	BM12125S	M12×1.75	125	65	15	100	4,370
38858	BM12150S	M12×1.75	150	65	15	120	6,030

ベースエレメント

クランプユニット

ロケータイング
エレメントクランプ
パーツ

補助ベース

マシンバイス

ボール盤バイス

技術資料

索引