



SILVYN® HCC



Benefits

- Dimensionally stable
- Flexible
- Lightweight
- Crush-resistant

Application range

- Mechanical engineering
- Apparatus construction
- Building Automation
- Moving applications
- Outdoors

Product features

- Conduit with full metric design
- Halogen and cadmium-free
- Abrasion-resistant
- High resistance to oil, petrol, acids and other chemicals

Product Make-up

- Fine-profile corrugated polyamide 6 conduit

Note

- UV-resistant and weather-resistant

Technical data

	ETIM 5.0 Class-ID: EC001175 ETIM 5.0 Class-Description: Corrugated plastic hose
	Colour delivered Black (RAL 9005), UV-resistant
	Material PA6 Halogen-free
	Temperature range -25°C to +100°C

Article number	Article designation	Nominal size	ID x OD mm	Bending radius (mm)	Suitable for SILVYN® FPAG-M / FLEXILOK-M	Suitable for SILVYN® HG-M / HW-M	PU ring (m)
SILVYN® HCC							
61793970	12	12	8,9 x 13.0	25	12		50
61793980	16	16	11,1 x 16.0	30	16		50
61793990	20	20	13,5 x 20.0	40	20		50
61794000	25	25	17,7 x 25.0	50	25		50
61794010	32	32	24,3 x 32.0	65		32	25
61794020	40	40	30,2 x 40.0	85		40	25
61794030	50	50	40,1 x 50.0	110		50	25
61794035	63	63	52,5 x 63.0	130		63	25

Photographs are not to scale and do not represent detailed images of the respective products.

Accessories

- SILVYN® FPAG-M refer to page 879
- SILVYN® HG-M refer to page 889
- SILVYN® HW-M refer to page 889
- SILVYN® FLEXILOK M refer to page 882
- SILVYN® FCL refer to page 885