


スィベルナット & グリップパット


SWIVEL NUT & GRIP PAD






品名 スィベルナット
材質 S45C
硬度 HRC35
仕上 黒染



品名 グリップパット
材質 SKH9
硬度 HRC60
仕上 黒染



品名 グリップパット
材質 SKH9
硬度 HRC60
仕上 黒染



(寸法表) 単位 長さ・ネジ径(mm) 質量約(g)							単位 長さ・ネジ径(mm) 質量約(g)							単位 長さ・ネジ径(mm) 質量約(g)						
No.	A	B	C	D	E	質量	No.	A	B	C	D	質量	No.	A	B	C	D	E	F	質量
SN-6	6-1.0	10	11.0	4	10	6	GAS-510	10		5	2.3	8	GBS-510	10	10	3.4	5	2.3	8.1	5
SN-8	8-1.25	13	14.0	6	13	11	GAS-612	12	10	6	3.0	10	GBS-612	12	12	4.0	6	3.0	9.6	8
SN-10	10-1.50	17	14.0	8	17	22	GAS-620	20		6	3.0	30	GBS-616	16	12	4.0	6	3.0	13.0	16
SN-12	12-1.75	19	16.5	10	19	31	GAS-625	25		6	3.0	43	GBS-620	20	12	4.0	6	3.0	16.3	25
SN-14	14-2.0	22	20.0	12	22	51	-	-	-	-	-	-	GBS-625	25	12	4.0	6	3.0	19.5	40
SN-16	16-2.0	24	24.0	14	24	69	-	-	-	-	-	-	-	-	-	-	-	-	-	-

レストナット

REST NUT






No.	質量(g)
12M-RN	42
16M-RN	63



No.	質量(g)
12M-PN	43
16M-PN	76



No.	質量(g)
12M-WN	43
16M-WN	80




(寸法表) RN・PN・WN				
A	B	C	D	E
M 12	20	22	19	13
M 16	25	28	24	16

材質 SCM440
硬度 HRC60
仕上 黒染

グリップスクリュー(A・Bタイプ)

GRIP SCREW A・B TYPE


Aタイプ



GAW
材質 SCM435
硬度 HRC32° ~ 38°
仕上 黒染

GBW
材質 SCM435
硬度 HRC32° ~ 38°
仕上 黒染

Bタイプ



(寸法表) 単位 長さ(mm) 質量約(g)								単位 長さ(mm) 質量約(g)							
No.	A	B	C	D	E	F	質量	No.	A	B	C	D	E	F	質量
-	-	-	-	-	-	-	-	GBW-625	25	6.0	10	7.9	M 6	2.3	8
-	-	-	-	-	-	-	-	GBW-825		7.3	13	9.5	M 8	3.0	15
GAW-1025	25				4		15	GBW-1025	25	8.4	17	12.7	M 10	3.0	30
GAW-1050	50	6.5	M 10	5	5	2.3	30	GBW-1040	40						35
GAW-1225	25				5		22	GBW-1225	25	9.5	19	15.9	M 12	3.0	35
GAW-1250	50	8.0	M 12	6	5	2.3	45	GBW-1240	40						50
GAW-1625	25				6		38	GBW-1635	35	12.0	24	19.1	M 16	3.0	85
GAW-1650	50	11.5	M 16	8	6	3.0	78	GBW-1650	50						100
GAW-2025	25				8		58	GBW-2040	40	14.5	30	25.4	M 20	3.0	160
GAW-2050	50	13.0	M 20	10	8	3.0	120	GBW-2060	60						205