




Specify Part No. by required thickness and length.  
(e.g.) Thickness is 20mm.

**SLI - 20300**  
Part No.


- This slide guide rail may be cut to the necessary dimension or bored for bolts.
- The movement direction is lengthwise.



■ Attachment type A



■ Attachment type B



Part No.	Thickness	Length	Width							Attachment type
	T	L	W	Tolerance	t	Tolerance	W <sub>1</sub>	Tolerance	W <sub>2</sub>	
<b>SLI-20300</b>	20	300	15	$\begin{matrix} -0.01 \\ -0.05 \end{matrix}$	11	$\begin{matrix} +0.05 \\ +0.02 \end{matrix}$	10	$\begin{matrix} 0 \\ -0.05 \end{matrix}$	5	A
<b>SLI-25300</b>	25	300	23	$\begin{matrix} -0.01 \\ -0.05 \end{matrix}$	10	$\begin{matrix} +0.05 \\ +0.02 \end{matrix}$	15	$\begin{matrix} 0 \\ -0.05 \end{matrix}$	8	B