


Diamond and CBN tools electroplated bond

Diamond grinding points



Conical pointed shape SK

The conical pointed shape SK is exceptionally well suited to deburring bores, regrinding centring holes and chamfering.



Recommendations for use:

- Dry grinding: 8–18 m/s
- Wet grinding: 15–25 m/s

Ordering notes:

- Please complete the description with the desired grit size.

PFERDVALUE:



| D x T [mm] | α | S_d [mm] | L_2 [mm] | Grit size | | Description |
|------------------------|----------|---------------|---------------|-------------|--------|----------------------|
| | | | | D 64 | D 126 | |
| | | | | EAN 4007220 | | |
| Shank dia. 6 mm | | | | | | |
| 6.0 x 45 | 7° | 6 | 50 | 354049 | 955970 | 1 DSK 6,0-7°/6 ... |
| 6.0 x 26 | 12° | 6 | 50 | 354056 | 955987 | 1 DSK 6,0-12°/6 ... |
| 6.0 x 21 | 15° | 6 | 50 | 354063 | 955994 | 1 DSK 6,0-15°/6 ... |
| 6.0 x 11 | 30° | 6 | 50 | 354032 | 354070 | 1 DSK 6,0-30°/6 ... |
| 6.0 x 5 | 60° | 6 | 50 | 393390 | 956007 | 1 DSK 6,0-60°/6 ... |
| 10.0 x 9 | 60° | 6 | 50 | 806128 | 806135 | 1 DSK 10,0-60°/6 ... |
| 10.0 x 5 | 90° | 6 | 50 | 806142 | 806159 | 1 DSK 10,0-90°/6 ... |
| 15.0 x 13 | 60° | 6 | 50 | 806166 | 806173 | 1 DSK 15,0-60°/6 ... |
| 15.0 x 7.5 | 90° | 6 | 50 | 806180 | 806197 | 1 DSK 15,0-90°/6 ... |



Diamond grinding point set

The set contains 10 diamond grinding points with grit size D 126 in the most common shapes and dimensions. The sturdy plastic box protects the tools from dirt and damage.


Contents:

- 1 piece each:
 - DZY-A 1,0-4/3 D 126
 - DZY-A 2,0-4/3 D 126
 - DZY-N 4,0-5/3 D 126
 - DZY-N 5,0-5/3 D 126
 - DZY-N 14,0-1,1/3 D 126
 - DKU-A 2,0/3 D 126
 - DKU-A 4,0/3 D 126
 - DKU-N 6,0/3 D 126
 - DSPG 3,0-7/3 D 126
 - DKT 3,0-8°/3 D 126

Recommendations for use:

- Dry grinding: 8–18 m/s
- Wet grinding: 15–25 m/s

PFERDVALUE:



| S_d [mm] | Grit size | | Description |
|---------------|-----------|--|----------------|
| | D 126 | | |
| EAN 4007220 | | | |
| 3 | 103845 | | 1 D-Set/3 D126 |