

Different bore type

more compact and lighter with combination of different diameter shaft (link from $\phi 6 \sim \phi 35$) (———— : pipe hole)

CS($\phi 6 \cdot \phi 9$) series

(stainless-steel bolt M3·M4)
When you use the parts for a clockwise and anticlockwise rotation as a pair, it is easy to clamp a screw.

<p>CS200,CS201</p> <p>Cross 90° hole for right-angle shaft attachment</p> <p>Screw cap to be on the opposite side against CS200</p> <p>CS200 CS201 $\phi 15 \times 30$</p>	<p>CS202,CS203</p> <p>Cross 45° hole for use in pairs, for attachment to diagonally</p> <p>To use in pairs with type CS202</p> <p>CS202 (45° left) CS203 (45° right) $\phi 15 \times 30$</p>	<p>CS204,CS204M</p> <p>One-sided boss</p> <p>A combination of other parts is available at a free angle.</p> <p>$\phi 15 \times 19 + L$</p> <table border="1"> <tr> <th>Part No.</th> <th>L</th> </tr> <tr> <td>CS204</td> <td>14</td> </tr> <tr> <td>CS204M</td> <td>25</td> </tr> </table>	Part No.	L	CS204	14	CS204M	25
Part No.	L							
CS204	14							
CS204M	25							

<p>CS209</p> <p>Vertical-horizontal hole for frame support or T-shape attachment.</p> <p>$\phi 15 \times 24$</p>	<p>CS214,CS215</p> <p>Strut 45° for use in pairs. For attachment with inclined angle</p> <p>To use in pairs with type CS214</p> <p>CS214 (45° right) CS215 (45° left) $\phi 15 \times 25$</p>
--	---

<p>CS250,CS251</p> <p>3 direction hole for multistage assembly of rack or frame</p> <p>CS250 CS251 $\phi 15 \times 36$</p>	<p>CS254</p> <p>Horizontal two-shaft hole for shaft or 204 attachment</p> <p>$\phi 15 \times 29$</p>	<p>CS352</p> <p>Corner for external tightening to set the corner of frame assembly</p> <p>$23 \times 23 \times 18$</p>
--	--	--

<p>CS401</p> <p>Split T to tuck without disassembling frame (capable of later attachment)</p> <p>$24 \times 20 \times 16$</p>	<p>CS402</p> <p>Split Cross to tuck without disassembling frame (capable of later attachment)</p> <p>$24 \times 20 \times 16$</p>	<p>CS604</p> <p>Joint for additional joint of shaft</p> <p>$18 \times 19 \times 13$</p>	<p>CS722</p> <p>Vertical-horizontal hole for frame support or T-shape attachment.</p> <p>$19 \times 13 \times 22$</p>
---	---	---	---

<p>PM217 (For $\phi 9$)</p> <p>Round-internal cap (black)</p> <p>Material: resin 1 bag for 4 parts</p> <p>$\phi 10 \times 12$</p>	<p>PM415,PM415L</p> <p>Screw with handle in case of high-frequency for tightening</p> <p>Material = SUS304</p> <table border="1"> <tr> <th>Part No.</th> <th>L</th> </tr> <tr> <td>PM415</td> <td>25</td> </tr> <tr> <td>PM415L</td> <td>29.5</td> </tr> </table>	Part No.	L	PM415	25	PM415L	29.5
Part No.	L						
PM415	25						
PM415L	29.5						

● For 300, 400 type, please match the mark on both edge phase on assembly.

Dimensional drawing (shape and measurement by size)

CS($\phi 6 \cdot \phi 9$) series