


# CoroMill® 331 insert for slotting

KRINS 90°



			Ordering code	P												M					K				N				S				H				Dimensions, mm, inch			
				1025	1030	4230	4240	530	1025	1030	1040	2030	2040	530	1020	3040	3040	3220	3330	H13A	1025	1030	H10	H13A	1025	1030	2030	2040	H13A	S30T	S40T	1030	3040	530	W1	LE	S			
Light		04	0.5	0.4	N331.1A-04 35 05H-PL			☆	☆																									9.5	4.6	3.50				
			.020	.016																														.374	.181	.138				
		05	0.8	1.2	N331.1A-05 45 08H-PL			☆	☆																										9.5	5.7	4.45			
			.031	.047																															.374	.224	.175			
		08	0.8	1.2	N331.1A-08 45 08H-PL			☆	☆																											9.5	7.7	4.45		
			.031	.047																																.374	.303	.175		
			11	0.8	1.2	N331.1A-11 50 08H-PL			☆	☆																									11.5	10.7	4.95			
			.031	.047																																.453	.421	.195		
	14		0.8	1.2	N331.1A-14 50 08H-PL			☆	☆																											11.5	13.7	4.95		
			.031	.047																																	.453	.539	.195	
	04		0.5	0.4	N331.1A-04 35 05H-ML							☆	☆	☆																						9.5	4.6	3.50		
			.020	.016																																	.374	.181	.138	
		05	0.8	1.2	N331.1A-05 45 08H-ML																														9.5	5.7	4.45			
		.031	.047																																	.374	.224	.175		
08		0.8	1.2	N331.1A-08 45 08H-ML																																9.5	7.7	4.45		
		.031	.047																																		.374	.303	.175	
11		0.8	1.2	N331.1A-11 50 08H-ML																																11.5	10.7	4.95		
		.031	.047																																	.453	.421	.195		
		14	0.8	1.2	N331.1A-14 50 08H-ML																														11.5	13.7	4.95			
		.031	.047																																	.453	.539	.195		
04		0.5	0.4	N331.1A-04 35 05E-KL											☆	☆	☆	☆																	9.5	4.6	3.50			
		.020	.016																																		.374	.181	.138	
05		0.8	1.2	N331.1A-05 45 08E-KL																																	9.5	5.7	4.45	
		.031	.047																																		.374	.224	.175	
		08	0.8	1.2	N331.1A-08 45 08E-KL																															9.5	7.7	4.45		
		.031	.047																																		.374	.303	.175	
11		0.8	1.2	N331.1A-11 50 08E-KL																																11.5	10.7	4.95		
		.031	.047																																		.453	.421	.195	
14		0.8	1.2	N331.1A-14 50 08E-KL																																	11.5	13.7	4.95	
		.031	.047																																		.453	.539	.195	
		04	0.5	0.4	N331.1A-04 35 05H-WL	☆	☆																												9.5	4.6	3.50			
		.020	.016																																		.374	.181	.138	
05		0.8	1.2	N331.1A-05 45 08H-WL	☆	☆																															9.5	5.7	4.45	
		.031	.047																																			.374	.224	.175
08		0.8	1.2	N331.1A-08 45 08H-WL	☆	☆																															9.5	7.7	4.45	
		.031	.047																																			.374	.303	.175
		11	0.8	1.2	N331.1A-11 50 08H-WL	☆	☆																													11.5	10.7	4.95		
		.031	.047																																		.453	.421	.195	
14		0.8	1.2	N331.1A-14 50 08H-WL	☆	☆																															11.5	13.7	4.95	
		.031	.047																																			.453	.539	.195

Q5 J474 J508 Q1 Q17