



# CoroMill® 300 face milling cutter

Cylindrical shank

Positive design



## Metric version

										Dimensions							
DC	CZC <sub>MS</sub>	APMX <sub>EFW</sub>	APMX <sub>FFW</sub>	AZ	RMPX	CNSC	Ordering code		DCON	DCX	LF	Nm	Kg	RPMX	CICT	MIID	
15.0	10	20	7.5	5.0	2.3	13°	1	2	R300-025A20-10M	20.0	25.0	150.0	3.0	0.50	2850	2	R300-1032..
17.0	08	20	6.0	4.0	1.9	8°	1	3	R300-025A20-08M	20.0	25.0	150.0	1.2	0.44	7200	3	R300-0828..
20.0	12	25	9.0	6.0	3.0	12°	1	3	R300-032A25-12H	25.0	32.0	150.0	3.0	0.65	3550	3	R300-1240..
	12	25	9.0	6.0	3.0	12°	1	2	R300-032A25-12M	25.0	32.0	190.0	3.0	1.18	8900	2	R300-1240..
22.0	10	25	7.5	5.0	2.3	7°	1	4	R300-032A25-10H	25.0	32.0	150.0	3.0	0.70	2850	4	R300-1032..
	10	25	7.5	5.0	2.3	7°	1	3	R300-032A25-10M	25.0	32.0	190.0	3.0	0.70	1470	3	R300-1032..
24.0	08	25	6.0	4.0	1.9	5°	1	5	R300-032A25-08H	25.0	32.0	150.0	1.2	0.63	3590	5	R300-0828..
	08	25	6.0	4.0	1.9	5°	1	4	R300-032A25-08M	25.0	32.0	190.0	1.2	0.79	9000	4	R300-0828..
28.0	12	32	9.0	6.0	3.0	8°	1	3	R300-040A32-12M	32.0	40.0	250.0	3.0	1.90	1140	3	R300-1240..
	12	32	9.0	6.0	3.0	8°	1	4	R300-040A32-12H	32.0	40.0	150.0	3.0	1.62	2850	4	R300-1240..

## Inch version

										Dimensions, inch							
DC	CZC <sub>MS</sub>	APMX <sub>EFW</sub>	APMX <sub>FFW</sub>	AZ	RMPX	CNSC	Ordering code		DCON	DCX	LF	Ft/lbs	Lbs	RPMX	CICT	MIID	
.625	09	1	.281	.177	.079	8°	1	2	RA300-025O25-09M	1.000	1.000	7.500	2.2	2.02	14500	2	R300-09..
	09	1	.281	.177	.079	8°	1	3	RA300-025O25-09H	1.000	1.000	6.000	2.2	1.67	27400	3	R300-09..
.750	13	1 1/4	.375	.248	.110	12°	1	2	RA300-032O32-13M	1.250	1.250	10.000	2.2	1.67	7400	2	R300-13..
	13	1 1/4	.375	.248	.110	12°	1	3	RA300-032O32-13H	1.250	1.250	6.000	2.2	1.67	25100	3	R300-13..
.875	09	1 1/4	.281	.177	.079	5°	1	3	RA300-032O32-09M	1.250	1.250	10.000	2.2	1.67	7400	3	R300-09..
	09	1 1/4	.281	.177	.079	5°	1	4	RA300-032O32-09H	1.250	1.250	6.000	2.2	1.68	27400	4	R300-09..
1.000	13	1 1/4	.375	.248	.110	8°	1	3	RA300-038O32-13M	1.250	1.500	10.000	2.2	3.08	7400	3	R300-13..
	13	1 1/4	.375	.248	.110	8°	1	4	RA300-038O32-13H	1.250	1.500	6.000	2.2	2.51	21600	4	R300-13..
1.125	09	1 1/4	.281	.187	.079	7°	1	4	RA300-038O32-09H	1.250	1.500	6.000	2.2	2.51	27400	4	R300-09..

