



CoroMill® 216 ball nose milling cutter

Weldon



Metric version

DC	CZC ₁₆	APMX	RMPX	AZ	CNCS	Ordering code	Dimensions								CICT _{SP}	MID _{SP}			
							DCON	DCX	LF	LU	Nm	KG	RPMX	CICT _{BALL}			MID _{BALL}		
12.0	12	20	10.8	85°	6.0	0	2	R216-12B20-040	20.0	12.0	91.0	21.2	1.2	0.20	21000	2	R216-12 02		
	12	20	10.8	85°	6.0	0	2	R216-12B20-060	20.0	12.0	111.0	24.0	1.2	0.20	21000	2	R216-12 02		
16.0	16	20	14.4	85°	8.0	1	2	R216-16B20-060	20.0	16.0	111.0	33.8	1.2	0.20	20000	2	R216-16 03		
	16	20	14.4	85°	8.0	1	2	R216-16B20-040	20.0	16.0	91.0	28.2	1.2	0.20	20000	2	R216-16 03		
20.0	20	25	17.9	85°	10.0	1	2	R216-20B25-070	25.0	20.0	127.0	40.6	2.0	0.38	24000	2	R216-20 T3		
	20	25	17.9	85°	10.0	1	2	R216-20B25-060	25.0	20.0	107.0	36.2	2.0	0.30	24000	2	R216-20 T3		
25.0	25	25	22.3	85°	12.5	1	2	R216-25B25-080	25.0	25.0	137.0	80.0	3.0	0.38	24000	2	R216-25 04		
	25	25	22.3	85°	12.5	1	2	R216-25B25-060	25.0	25.0	117.0	60.0	3.0	0.38	24000	2	R216-25 04		
30.0	30	16	32	26.9	85°	15.0	1	2	R216-30B32-100	32.0	30.0	161.0	90.4	5.0	0.70	19500	2	R216-30 06	1 APMT 160408-M
	30	16	32	26.9	85°	15.0	1	2	R216-30B32-070	32.0	30.0	131.0	60.4	5.0	0.60	19500	2	R216-30 06	1 APMT 160408-M
32.0	32	32	28.6	85°	16.0	1	2	R216-32B32-070	32.0	32.0	131.0	70.0	5.0	0.60	18500	2	R216-32 06		
	32	32	28.6	85°	16.0	1	2	R216-32B32-100	32.0	32.0	161.0	100.0	5.0	0.79	18500	2	R216-32 06		
40.0	40	16	40	36.5	85°	20.0	1	2	R216-40B40-150	40.0	40.0	221.0	150.0	7.5	1.86	8000	2	R216-40 07	2 APMT 160408-M
	40	16	40	36.5	85°	20.0	1	2	R216-40B40-100	40.0	40.0	171.0	100.0	7.5	1.42	8000	2	R216-40 07	2 APMT 160408-M
50.0	50	40	44.6	85°	25.0	1	2	R216-50B40-100	40.0	50.0	171.0	100.0	10.0	2.00	7000	2	R216-50 07		
	50	16	50	44.6	85°	25.0	1	2	R216-50B50-125	50.0	50.0	206.0	125.0	10.0	2.60	7000	2	R216-50 07	2 APMT 160408-M
50	16	50	44.6	85°	25.0	1	2	R216-50B50-175	50.0	50.0	256.0	175.0	10.0	3.10	7000	2	R216-50 07	2 APMT 160408-M	

