



- For work locating and stopping.
- Urethane pad is adhered.
- Impact is absorbed by the urethane pad.
- All products are provided with lock nut.

• Material/Finish

RoHS Compliant

	SUS
Thread Part	SCM435 Nickel Plating
Pad	Polyurethane (hardness: 90 HDA)
Lock Nut	SS400 Trivalent Chromate Treatment

## Dimensions

Unit : mm

Part Number	M (coarse)	t	L <sub>2</sub>	D <sub>1</sub>	B	C	B <sub>1</sub>	T	h	d <sub>1</sub>	Mass (g)
SUS-M4	M4	4.5	0.5	3.1	7	8.1	2	2.4	3	1.6	1.6 - 3.1
SUS-M5	M5	4.5	0.5	4	8	9.2	2.5	3.2	3	2.2	3 - 6.1
SUS-M6	M6	4.5	0.5	4.8	10	11.5	3	3.6	3	2.6	5.6 - 11
SUS-M8	M8	5.5	0.5	6.5	13	15	4	5	4	5.1	13 - 20
SUS-M10	M10	5.5	0.5	8.3	17	19.6	5	6	4	6.9	21 - 31

Part Number	L (mm)										
	10	15	20	25	30	35	40	45	50	60	
SUS-M4	●	●	●	●	●	●					
SUS-M5	●	●	●	●	●	●	●				
SUS-M6		●	●	●	●	●	●		●		
SUS-M8				●	●	●	●	●	●	●	
SUS-M10					●	●	●	●	●	●	

### • Related Products

A stopper bolt with bolt-type urethane pad **SUB** is available.  
 → P.534



- Part number specification

## SUS-M5-40

Product Code

Cleanroom Wash & Packaging → P.792	Screw Combination → P.798	Screw Length Adjustment → P.796	Vibration Resistant → P.795
Not Available	Available / Add'l charge	Not Available	Please feel free to contact us