


T-Max® P insert for turning

Rhombic 80°



		LE	S	RE	ISO CODE	P		M		K		S				ANSI CODE		
						4305	4315	4325	2015	2025	3210	3225	1105	1115	1125		H18A	S10F
	12 1/2	12.1	4.76	0.79	CNMG 12 04 08-WM	☆	☆	☆								CNMG 432-WM		
		.476	.187	.031														
		11.7	4.76	1.19	CNMG 12 04 12-WM	☆	☆	☆									CNMG 433-WM	
		.460	.187	.047														
		16 5/8	15.3	6.35	0.79	CNMG 16 06 08-WM		☆	☆								CNMG 542-WM	
		.603	.250	.031														
	16 5/8	14.9	6.35	1.19	CNMG 16 06 12-WM		☆	☆								CNMG 543-WM		
		.587	.250	.047														
		12 1/2	12.1	4.76	0.79	CNMG 12 04 08-WMX	☆					☆					CNMG 432-WMX	
		.476	.187	.031														
		11.7	4.76	1.19	CNMG 12 04 12-WMX	☆						☆					CNMG 433-WMX	
		.460	.187	.047														
	16 5/8	15.3	6.35	0.79	CNMG 16 06 08-WMX	☆					☆					CNMG 542-WMX		
		.603	.250	.031														
		14.9	6.35	1.19	CNMG 16 06 12-WMX	☆					☆	☆					CNMG 543-WMX	
		.587	.250	.047														
		12 1/2	12.1	4.76	0.79	CNMG 12 04 08-PM	☆											CNMG 432-PM
		.476	.187	.031														
	12 1/2	11.7	4.76	1.19	CNMG 12 04 12-PM	☆										CNMG 433-PM		
		.460	.187	.047														
		11.3	4.76	1.59	CNMG 12 04 16-PM	☆											CNMG 434-PM	
		.445	.187	.062														
		16 5/8	14.9	6.35	1.19	CNMG 16 06 12-PM	☆											CNMG 543-PM
		.587	.250	.047														
	12 1/2	12.1	4.76	0.79	CNMG 12 04 08-KM							☆				CNMG 432-KM		
		.476	.187	.031														
		11.7	4.76	1.19	CNMG 12 04 12-KM								☆				CNMG 433-KM	
		.460	.187	.047														
		11.3	4.76	1.59	CNMG 12 04 16-KM								☆				CNMG 434-KM	
		.445	.187	.062														
	16 5/8	15.3	6.35	0.79	CNMG 16 06 08-KM							☆				CNMG 542-KM		
		.603	.250	.031														
		14.9	6.35	1.19	CNMG 16 06 12-KM								☆				CNMG 543-KM	
		.587	.250	.047														
		14.5	6.35	1.59	CNMG 16 06 16-KM								☆					CNMG 544-KM
		.572	.250	.062														
	19 3/4	18.1	6.35	1.19	CNMG 19 06 12-KM							☆				CNMG 643-KM		
		.714	.250	.047														
		17.7	6.35	1.59	CNMG 19 06 16-KM								☆					CNMG 644-KM
		.699	.250	.062														

A65

L5

