

SROS One Side Pan Head Machine Screws




WEB Selection Tool

WEB CAD Download

Tamper Resistance

SUS Stainless steel



● Part number specification

SROS-M4-16



Order in number of packs.
The minimum order quantity is 1 piece. → P.794

- The screws can be installed, but not removed, using commercially available slotted screwdrivers.
- Remove the screws by using **SROT** Specialty Removal Tool.

● Application

Machinery, tools, equipment, and devices disassembly prevention · tampering prevention, theft prevention for outdoor facilities, security measures, and safety measures

● Material/Finish

RoHS Compliant

	SROS
Main Body	SUS304
Strength Class	Equivalent to A2-50

Part Number	M	L								D1	L1	Removal Tool Part No.	Mass (g)
		5	6	8	10	12	16	20	25				
SROS-M3	M3	5	6	8	10	12	16			5.5	2	SROT-410	0.49 - 0.94
SROS-M4	M4		6	8	10	12	16	20	25	7	2.6	SROT-410	1 - 2.5
SROS-M5	M5			8	10	12				9	3.3	SROT-510	2.2 - 2.7

Unit : mm


Part Number	Qty*1 per pack
SROS-M3	20
SROS-M4	20
SROS-M5	20

*1 The minimum order quantity is 1 piece. → P.794

● Dedicated driver

Unit : mm

Part Number	L	Mass (g)	Qty per pack
SROT-410	180	94	1
SROT-510	185	127	1



Individual Sales → P.794	Cleanroom Wash & Packaging → P.792	Screw Length Adjustment → P.796	Vibration Resistant → P.795	Modification process for captive use → P.791
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge