



# Multi Auto Clamps - Guide Bar Type [Series Type]



Part name	Material	Heat Treatment	Surface Treatment
Clamp Block	S50C	HRC50 heat treatment	-
Clamp pin	SKD11	HRC60 heat treatment	-


**Component Parts**




	Component Parts	Quantity
(1)	Clamp Block	1
(2)	Clamp pin (input)	1
(3)	Clamp pin (output)	1

**External Dimensions**

**Standard Type**



**Type with Return Mechanism**



**Specifications**


Type	Shape	Order No.	No.	Name	Tapped Hole		Weight (kg)
					Input Side	Output Side	
Standard		109780	MT121A	Guide Bar Type	Yes	Yes	0.19
		114533	MT122A	Guide Bar Type	Yes	No	0.20
Type with Return Mechanism		114460	MR121A	Main Body (Hole Type)	Yes	Yes	0.31

**Optional**

**Guide Bar MT12-AG**



**Extension Bar MT12-S**



\* For guide bars and extension bars, provide us with the A dimension and we will give you a separate quote.